

KERN ORM 1UN

Digital measurement of refraction index for universal application



Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-UN

Measuring System

Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Precision	0,0003 nD
	0,2 %
	0,002 sgU 0.2 g/dl
Measuring method	Total reflection
Measuring range Brix [Min]	0 %
Scales	Refractive index
	Brix
	Urine (spec. gravity)
	Serum proteïne
Measuring ranges	1,3330 nD - 1,4200 nD
	0,0 % - 50,0 %
	1,000 sgU - 1,050 sgU
	0,0 g/dl - 12,0 g/dl
Readabilites [d]	0,0001 nD
	0,1 %
	0,001 sgU
	0,1 g/dl
Readout Brix	0,1 %
Automatic temperature compensation (ATC)	✓
Accuracy Brix	±0,2 %
Measuring range refractive index [Min]	1,3330 nD
Measuring range refractive index [Max]	1,4200 nD

Readout refractive index	0,0001 nD
Accuracy refractive index	±0,0003 nD
Scale for Refractive index	✓
Measuring range protein serum [Min]	0 g/100 ml
Measuring range protein serum [Max]	12 g/100 ml
Readout protein serum	0,1 g/100 ml
Accuracy protein serum	±0,2 g/100 ml
Scale protein serum	✓
Measuring range urine (specific gravity) [Min]	1,000
Measuring range urine (specific gravity) [Max]	1,050
Readout urine (specific gravity)	0,001
Accuracy urine (specific gravity)	±0,002
Scale urine (specific gravity)	✓
Appropriate calibration liquid	0 % (distilled water)
Measuring range Brix [Max]	50 %
Brix scale	✓
Area of application	Urine

Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital
Prism lid	✓
Material prism	ZLaF3 lanthanum flint glass nd=1.85544

Functions

Averaging measurement	✓
Averaging measurement amount	15
IP protection - complete device	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec

Power Supply

Supplied power supply	Battery
Power supply cable removable	removable
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V
Battery - Number of cells	1
Battery - Individual weight	11,5 g
Battery - Total weight	11,5 g
Battery - Construction	Individual cells

KERN ORM 1UN



Digital measurement of refraction index for universal application

Battery capacity (Wh)	1,95 Wh
Battery – Lithium content	0 g
Battery/Accu connected	not connected, enclosed

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration	961-290
--	---------

Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Delivery time	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

Product information

GTIN/EAN number	404576 133556 1
Trade number	90275000
REACH classification	no prohibited substances

Pictograms

STANDARD

