

KERN 357-14

Individual weight, OIML Class M2, 10 kg, Knob, stainless steel fine turned



Category	
Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	357

Measuring System	
Test weight - volume (cm ³)	1190,4762
Test weight - Density uncertainty (kg/m ³)	140
Test weight - volume uncertainty (cm ³)	24,093
Weight OIML class	M2
Test weight - nominal value	10 kg
Permissible tolerance according to OIML (+/-)	1,6 g
Test weight - Density (kg/m ³)	7950
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

Construction	
Shape weight	Knob
Dimensions (Ø×H)	100×185 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)	
Article number for DAkkS calibration	962-644

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	115×115×198 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg

Optional cases

Case - Plastic article number	347-140-400
Case - Aluminium article number	317-140-600
Case - Wood article number	337-140-200

Product information

GTIN/EAN number	4045761289062
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

