

SAUTER TVM 20KN 120N-LB

KERN

Practical set for force-displacement-measurements in laboratory and industry



Category

Brand	Sauter
Product category	Test bench
Product group	Test stand set
Product family	TVM-LB

Measuring System

Measurable length [Max]	21 cm
Length measuring device	Length measuring device with display and data interface

Display

Display type	LED segments
Display type	7 segment LED
Display digit height - smallest digit	9 mm

Construction

Dimension (W×D×H)	400×256×1535 mm
Dimension housing (W×D×H)	400×256×1535 mm
Dimensions completely mounted (W×D×H)	400×256×1535 mm
Material housing	metal, lacquered
Material display housing	metal, lacquered
Type of drive	Electric motor
Mounting - force dissipation	Threaded hole M12 4 × threaded hole M10
Mounting - force application	Threaded hole - 1 × M12, 4 × M10
Generated force [Max]	20 kN
Transversal movement speed [Min]	30 mm/min

Transversal movement speed [Max]	120 mm/min
Transversal movement speed variation	3%
Measurement alignment	vertical
Guide column(s) distance	215 mm
Guide column(s) length	113,5 cm
Traverse distance [Max]	210 mm

Functions

Speed display	✓
Repeat function	✓
Limit switch	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - optional	EURO UK CH
Input voltage power supply / power [Max]	220 V AC, 50 Hz
Input voltage device / power [Max]	~220 V - 240 V AC; 50 Hz
Power socket for mains adapter	Power supply cable

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	520×345×1610 mm
Shipping method	Freight
Net weight approx.	75 kg
Gross weight approx.	90 kg
Shipping weight	88 kg

Product information

GTIN/EAN number	4045761362918
Trade number	90249000
REACH classification	no prohibited substances

SAUTER TVM 20KN 120N-LB



Practical set for force-displacement-measurements in laboratory and industry

Pictograms

STANDARD

