


Platforms KERN KFP · KXP



Other platform sizes, special construction, individual scale construction according to your individual requirements, also possible with third-party components, please enquire

1 KERN KFP-V20 IP65

Platform



- Stainless steel-weighing plate, **A** Painted steel base
- 1 load cell, aluminium, silicone-coated, IP65, OIML-R60-approved, class III, 3000 e
- Level indicator and levelling feet for precise levelling of the scale

2 KERN KXP-V20 IP65

Platform



- Stainless steel-weighing plate, **B** Painted steel base, extremely rigid, wing design
- 1 load cell, aluminium, silicone-coated, IP65, OIML-R60-approved, class III, 3000 e
- Level indicator and levelling feet for precise levelling of the scale



Model	Weighing range [Max] kg	Readability [d] g	Verification value [e] g	Min. load [Min] g	Cable length approx. m	Net weight approx. kg	Weighing plate W×D×H mm
KERN							
1 Platform KFP-V20 IP65							
KFP 3V20M	3	0,1	1	20	2,5	3,6	230×230×105
KFP 6V20M	6	0,2	1 2	40	2	3,6	230×230×105
KFP 6V20LM	6	0,2	1 2	40	2,5	6	300×240×105
KFP 15V20M	15	0,5	2 5	100	2	6	300×240×105
KFP 15V20LM	15	0,5	2 5	100	2,5	10	400×300×125
KFP 30V20SM	30	1	10	200	2,5	6	300×240×105
KFP 30V20M	30	1	5 10	200	2	10	400×300×125
KFP 60V20M	60	2	10 20	400	2	10	400×300×125
KFP 60V20LM	60	2	10 20	400	2	10	500×400×130
KFP 150V20M	150	5	20 50	1000	2	10	500×400×130
KFP 150V20LM	150	5	20 50	1000	2	22	650×500×135
KFP 300V20M	300	10	50 100	2000	2	22	650×500×135
KFP 600V20AM	600	20	200	4000	2,5	46	800×600×190
2 Platform KXP-V20 IP65							
KXP 6V20LM *	6	0,2	1 2	40	3	3,2	300×240×90
KXP 15V20M *	15	0,5	2 5	100	3	3,2	300×240×90
KXP 15V20LM *	15	5	5	100	3	8	400×300×90
KXP 30V20M *	30	1	5 10	200	3	8	400×300×90
KXP 30V20LM *	30	1	5 10	200	3	18	500×400×123
KXP 60V20M *	60	2	10 20	400	3	11	400×300×90
KXP 60V20LM *	60	2	10 20	400	3	22	500×400×123
KXP 150V20M *	150	5	20 50	1000	3	18	500×400×123
KXP 150V20LM *	150	5	20 50	1000	3	34	650×500×133,5
KXP 300V20M *	300	10	50 100	2000	3	34	650×500×133,5

! * ONLY WHILE STOCKS LAST!



Internal adjusting:

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required



Easy Touch:

Suitable for the connection, data transmission and control through PC or tablet.



Memory:

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



Alibi memory:

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



KERN Universal Port (KUP):

allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WLAN, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort



Data interface RS-232:

To connect the balance to a printer, PC or network



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



USB data interface:

To connect the balance to a printer, PC or other peripherals



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals



WiFi data interface:

To transfer data from the balance to a printer, PC or other peripherals



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Analogue interface:

to connect a suitable peripheral device for analogue processing of the measurements



Interface for second balance:

For direct connection of a second balance



Network interface:

For connecting the scale to an Ethernet network



KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO log:

The balance displays weight, date and time, independent of a printer connection



GLP/ISO log:

With weight, date and time. Only with KERN printers.



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight



Recipe level A:

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



Recipe level B:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display



Totalising level A:

The weights of similar items can be added together and the total can be printed out



Percentage determination:

Determining the deviation in % from the target value (100 %)



Weighing units:

Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details



Weighing with tolerance range:

(Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



Hold function:

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram.



Suspended weighing:

Load support with hook on the underside of the balance



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Universal plug-in power supply:

with universal input and optional input socket adapters for
A) EU, CH, GB
B) EU, CH, GB, USA
C) EU, CH, GB, USA, AUS



Plug-in power supply:

230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available



Integrated power supply unit:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body



Weighing principle: Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



Weighing principle: Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



Weighing principle: Single cell technology:

Advanced version of the force compensation principle with the highest level of precision



Verification possible:

The time required for verification is specified in the pictogram



DAkkS calibration possible (DKD):

The time required for DAkkS calibration is shown in days in the pictogram



Factory calibration (ISO):

The time required for Factory calibration is shown in days in the pictogram



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram