

KERN KXC-TM

Stainless steel display device with IP68 dust and spray protection and up to four interfaces, with optional verification



Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction	
Dimension display device (W×D×H)	232×150×77,3 mm
Material display housing	stainless steel
Stand rotatable	no
Stand inclinable	no
Wall mount	✓

Functions	
PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓

Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	IP68
IP protection - display	IP68
	5 min 2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min 30 min 60 min 30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	7

Interface	
Interfaces	RS-232 (optional, factory)

Category	
Brand	KERN
Product category	Component
Product group	Display device
Product family	KXC

Measuring System	
Number of weighing ranges	2
Indicator configuration	SingleRange MultiRange MultiInterval
Conformity assessment possible	✓
Terminal resolution (not verifiable)	999.999
Terminal resolution (verifiable)	3.000
Adjustment options	Adjusting with external weight
Linearisation in dots	3
Units (if device is conformity assessed)	kg g
Units	kg g ffa PCS %
Default unit	kg
Load cell - load cell resistance [Min] (Ohm)	87
Load cell - load cell resistance [Max] (Ohm)	1227

Display	
Display type	LCD
Display type	LCD with backlight

KERN KXC-TM



Stainless steel display device with IP68 dust and spray protection and up to four interfaces, with optional verification

Ethernet (optional, factory)
 WiFi (optional, factory)
 Alibi memory (optional, factory)
 analogue (0 - 10 V) (optional, factory)
 analogue (4 - 20 mA) (optional, factory)
 Bluetooth BLE (v4.0) (optional, factory)
 USB-Device (optional, factory)

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	330×275×180 mm
Shipping method	Parcel service
Net weight approx.	1,6 kg
Gross weight approx.	2,4 kg
Shipping weight	3,3 kg

Product information

GTIN/EAN number	4045761360358
Trade number	84239010
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY



Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Input voltage power supply / power [Max]	110 V - 240 V AC
Power supply cable removable	fixed connection
Power socket for mains adapter	Cable permanently installed
Battery / accumulator type	Li-Ion
Battery	no battery
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III

Services (optional)

Article number for adjustment at the location of installation	auf Anfrage on request
---	--------------------------