

# SAUTER TVM 5000N230NL-LB

# KERN

Practical set for force-displacement-measurements in laboratory and industry



Transversal movement speed [Max]	230 mm/min
Transversal movement speed variation	3%
Measurement alignment	vertical
Guide column(s) distance	215 mm
Guide column(s) length	113,5 cm
Traverse distance [Max]	210 mm

## Functions

Speed display	✓
Repeat function	✓
Length measuring - zero setting	✓
Limit switch	✓

## Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - optional	EURO UK CH
Input voltage power supply / power [Max]	220 V AC, 50 Hz
Input voltage device / power [Max]	~220 V - 240 V AC; 50 Hz
Power socket for mains adapter	Power supply cable

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

## Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	520×340×1610 mm
Shipping method	Freight
Net weight approx.	65 kg
Gross weight approx.	80 kg
Shipping weight	80 kg

## Product information

GTIN/EAN number	4045761362932
Trade number	90249000

## Category

Brand	Sauter
Product category	Test bench
Product group	Test stand set
Product family	TVM-LB

## Measuring System

Measurable length [Max]	21 cm
Length measuring device	Length measuring device with display and data interface

## Display

Display type	LED segments
Display type	7 segment LED
Display digit height - smallest digit	9 mm

## Construction

Dimension (W×D×H)	400×256×1535 mm
Dimension housing (W×D×H)	400×256×1535 mm
Dimensions completely mounted (W×D×H)	400×256×1535 mm
Material housing	metal, lacquered
Material display housing	metal, lacquered
Type of drive	Electric motor
Mounting - force dissipation	Threaded hole M12 4 × threaded hole M6
Mounting - force application	Threaded hole - 1 × M12, 4 × M6
Generated force [Max]	5 kN
Transversal movement speed [Min]	10 mm/min

# SAUTER TVM 5000N230NL-LB



Practical set for force-displacement-measurements in laboratory and industry

REACH classification

no prohibited substances

Pictograms

STANDARD

---

