



B7CA-SFAL-42015 - Circuit Breaker, Square D, 15A, FAL4, 2 Pole 480V

By Killark
Catalog # B7CA-SFAL-42015

Circuit Breaker, Square D, 15A, FAL4, 2 Pole 480V



Features

- Copper-free, cast aluminum construction (less than 4/10 of 1%).
- High strength, lighter in weight, corrosion resistant.
- Hinged Cover is standard (left side hinge).
- More wiring room - Meets the latest NEC/CEC wire bending requirements for circuit breaker enclosures.
- Ductile Mounting Lugs - Lugs are made of ductile aluminum alloy to adjust to irregular mounting surfaces without damage to enclosure.
- Universal Mounting Pan - Sheet aluminum pan is pre-drilled to facilitate easy field installation of major circuit breaker brands.
- Provision for grounding supplied as standard.
- Conduit Openings Supplied - Standard conduit openings include power conduit top and bottom and a plugged opening suitable for field installation of drain and breather.
- Special conduit openings can be supplied at factory, or can be field installed.
- Breaker Handle - Provisions for lock "ON" or "OFF" positions with up to three padlocks. Spring loaded to prevent damage of breaker toggle and provides positive handle alignment. O-ring on shaft to prevent water seeping into enclosure.
- Recessed Flange Notches - Flanges are notched to allow for easier cover opening with prying instrument without flange damage.
- Gasketed Flange - Nitrile (BUNA-N) O-ring gasket is located inside cover bolt circle to prevent water seeping into enclosure.
- Quick Release, Captivated Cover - Bolts of 316 Grade Stainless Steel Triple lead bolts require only 3 1/2 turns to disengage.

Application

Locations such as petroleum refineries, chemical and petroleum plants with indoor and outdoor processes. Motor control and circuit protection in locations made hazardous due to the presence of flammable gases or vapors, combustible dust, or easily ignitable fiber and flyings, and areas which are subject to corrosion, weather, and dampness.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA
---------------------	---

EU RoHS Indicator	Class II, Divisions 1 & 2, Groups E, F, G
Nema Rating	Class III, Divisions 1 & 2
UL File Number	Contact Manufacturer
CSA File Number	3, 4, 4X, 7(B, C, D), 9(E, F, G)
Buy America(n) Qualified	E83969
	LR11714
	Contact Manufacturer
Conductor	
Number Of Wires	3
Number Of Poles	2
Current	
Primary Voltage	480 VAC/250 VDC
Amperage Rating	15 A
Frequency Rating	60 Hz
Dimensions	
Depth	9.125 in
Width	11 in
Weight	46 lb.
Height	18 in
General	
Type	Circuit Breaker Enclosure
Enclosure Type	Bolted
Series	B7C Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Lacquer
UPC	783936096933
Color	Aluminum
Mounting Type	Wall
Operational	
Operating Temperature Celcius	40 Degree
Max	
Action	DP
Actuator	Molded Case Circuit Breaker Operator

Product Assets

- Catalog [English]
 - Catalog Page [English]
 - Installation Manual [English]
 - Installation Manual [English]
-

