



B7CE-WLD-62400 - B7C Series, 400 A, 600 VAC, 2 Pole, LD Frame, Circuit Breaker Enclosure

By Killark
Catalog # B7CE-WLD-62400

B7C Series,400 A, 600 VAC, 2 Pole, LD Frame, Circuit Breaker Enclosure

Features

- Copper-free, cast aluminum construction (less that 4/10 of 1%).
- High strength, lighter in weight, corrosion resistant.
- Hinged Cover is standard (left side hinge).
- More wiring room - Meets the latest NEC/CEC wire bending requirements for circuit breaker enclosures.
- Ductile Mounting Lugs - Lugs are made of ductile aluminum alloy to adjust to irregular mounting surfaces without damage to enclosure.
- Universal Mounting Pan - Sheet aluminum pan is pre-drilled to facilitate easy field installation of major circuit breaker brands.
- Provision for grounding supplied as standard.
- Conduit Openings Supplied - Standard conduit openings include power conduit top and bottom and a plugged opening suitable for field installation of drain and breather.
- Special conduit openings can be supplied at factory, or can be field installed.
- Breaker Handle - Provisions for lock "ON" or "OFF" positions with up to three padlocks. Spring loaded to prevent damage of breaker toggle and provides positive handle alignment. O-ring on shaft to prevent water seeping into enclosure.
- Recessed Flange Notches - Flanges are notched to allow for easier cover opening with prying instrument without flange damage.
- Gasketed Flange - Nitrille (BUNA-N) O-ring gasket is located inside cover bolt circle to prevent water seeping into enclosure.
- Quick Release, Captivated Cover - Bolts of 316 Grade Stainless Steel Triple lead bolts require only 3 1/2 turns to disengage.

Application

Locations such as petroleum refineries, chemical and petroleum plants with indoor and outdoor processes. Motor control and circuit protection in locations made hazardous due to the presence of flammable gases or vapors, combustibile dust, or easily ignitable fiber and flyings, and areas which are subject to corresion, weather, and dampness.

Specifications

- Hazardous Rating(s)
- Class I, Divisions 1 & 2, Groups B, C, D
 - Class I, Zones 1 & 2, Groups IIB+H2, IIA



EU RoHS Indicator		• Class II, Divisions 1 & 2, Groups E, F, G
Nema Rating		• Class III, Divisions 1 & 2
UL File Number		Contact Manufacturer
CSA File Number		3, 4, 4X, 7(B, C, D), 9(E, F, G)
Buy America(n) Qualified		E83969
		LR11714
		Contact Manufacturer
Conductor		
Number Of Wires	3	
Number Of Poles	2	
Current		
Primary Voltage	600 VAC/250 VDC	
Amperage Rating	400 A	
Frequency Rating	60 Hz	
Dimensions		
Depth	9.625 in	
Width	17.5 in	
Weight	215 lb.	
Height	45.375 in	
General		
Type	Circuit Breaker Enclosure	
Enclosure Type	Bolted	
Series	B7C Series	
Material	Aluminum, Copper Free (less than 4/10 of 1%)	
Finish Type	Lacquer	
UPC	783936099408	
Color	Aluminum	
Mounting Type	Wall	
Operational		
Operating Temperature Celcius	40 Degree	
Max		
Action	DP	
Actuator	Molded Case Circuit Breaker Operator	

Product Assets

- Catalog [English]
 - Catalog Page [English]
 - Installation Manual [English]
 - Installation Manual [English]
-

