



DVL1330X1G - DVL Series LED Dust Tight / Utility Hazardous Rated 13 Watt, 120-277 VAC 5000K, 1144 Lumens

By Killark
Catalog # [DVL1330X1G](#)

DVL Series LED Dust Tight/ UtilityHazardous Rated 13 Watt, 120-277 VAC 5000K, 1144 Lumens

Features

- Compact in Size with Traditional Industrial Appearance and Suitability
- DVL LED Housings can be retrofitted to existing DV Series splice boxes to upgrade from incandescent housing 100 Series components
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class II, Division 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Lumens Per Watt	88
Wattage	13 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	1/2"
----------	------

General

Series	DVL Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Optic Type	Glass Globe - Clear
UPC	783936084145
Light Source	LED
Mounting Type	Ceiling

Operational

Lumens	1144
Lumen Range	0-2,000 lm

Product Assets

[Catalog \[English\]](#)

