



DEDS-100AA - DEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 2 Aux Contacts

By Killark
Catalog # [DEDS-100AA](#)

DEDS Series, 100 Amp Max, Non-Fused Disconnect Switch W/ 2 Aux Contacts

Features

- Bolted and gasketed cabinet type construction insures the exclusion of conductive or combustible dusts from entering the assembly.
- Enclosure and external handle is copper-free aluminum alloy (less than 4/10 or 1%).
- Cover bolts are stainless steel.
- External handle is vault type with standard provisions for locking in the "OFF" position with up to three padlocks.
- Provisions for locking in "ON" position available as factory modification (Add suffix SU40 to catalog number).
- Eaton (Cutler-Hammer) Type DS Switches.
- Two cast conduit hubs, one top and one bottom.
- Internal disconnect handle mechanism is a sliding plate mounted to the cover.

Specifications

Hazardous Rating(s)	• Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290
CSA File Number	LR11714
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	4
-----------------	---



Number Of Poles	3
Current	
Primary Voltage	600 VAC/250 VDC
Frequency Rating	60 Hz

Dimensions	
Depth	7 in
Width	7.75 in
Weight	19.5 lb.
Height	15.375 in

General	
Type	Non-Fused Disconnect
Enclosure Type	Bolted
Series	DEDS Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936116501
Mounting Type	Wall

Operational	
Operating Temperature Celcius Max	40 Degree

Product Assets

[Catalog \[English\]](#)