



ALUMINUM - CONDUIT BODIES

UL - Standard 514B
 SB - C22.2 #18

FEATURES-SPECIFICATIONS

Applications

- For use on threaded rigid/IMC conduit
- Use conduit bodies for making turns in conduit systems, connecting conduit sections, as pull outlets, and to provide openings for maintenance and making taps and splices to conductors



Features

- Flat back design for easy mounting close to walls
- Cast of high strength, corrosion and weather resistant aluminum alloy with painted finish
- May be used on aluminum or steel conduit
- Lightweight, makes installation simple



Type LB

TYPE LB							
CATALOG NUMBER	CONDUIT SIZE	DIMENSIONS					
		A	B	C	D	E	F
EALB-1	1/2"	1-5/16"	3-7/8"	1/2"	2-1/8"	4-3/8"	1-1/16"
EALB-2	3/4"	1-1/2"	4-5/8"	3/4"	2-7/16"	5-1/8"	1-11/32"
EALB-3	1"	1-3/4"	5-3/8"	1"	2-13/16"	5-15/16"	1-21/32"
EALB-4	1-1/4"	2-1/2"	6-5/8"	1-1/4"	3-3/4"	6-7/8"	2-1/4"
EALB-5	1-1/2"	2-1/2"	6-5/8"	1-1/2"	3-3/4"	6-7/8"	2-1/4"
EALB-6	2"	3-1/8"	8-1/2"	2"	4-1/8"	9-7/32"	2-15/16"
EALB-7	2-1/2"	4-9/16"	12-1/4"	2-1/2"	5-13/16"	13-1/8"	3-7/16"
EALB-8	3"	4-9/16"	12-1/4"	3"	5-13/16"	13-1/8"	4-7/64"
EALB-9	3-1/2"	5-7/16"	14-7/8"	3-1/2"	7-1/4"	15-3/8"	5-9/64"
EALB-10	4"	5-7/16"	14-7/8"	4"	7-1/4"	15-3/8"	5-9/64"



Type C

TYPE C							
CATALOG NUMBER	CONDUIT SIZE	DIMENSIONS					
		A	B	C	D	E	F
EAC-1	1/2"	1-5/16"	3-7/8"	1/2"	1-7/16"	4-29/32"	1-1/16"
EAC-2	3/4"	1-1/2"	4-5/8"	3/4"	1-11/16"	5-1/2"	1-11/32"
EAC-3	1"	1-3/4"	5-3/8"	1"	1-15/16"	6-7/16"	1-21/32"
EAC-4	1-1/4"	2-1/2"	6-5/8"	1-1/4"	2-7/8"	8-7/16"	2-1/4"
EAC-5	1-1/2"	2-1/2"	6-5/8"	1-1/2"	2-7/8"	8-7/16"	2-1/4"
EAC-6	2"	3-1/8"	8-1/2"	2"	3-7/16"	10-3/4"	2-15/16"
EAC-7	2-1/2"	4-9/16"	12-1/4"	2-1/2"	4"	14"	3-7/16"
EAC-8	3"	4-9/16"	12-1/4"	3"	4-3/4"	13-1/2"	4-7/64"
EAC-9	3-1/2"	5-7/16"	14-7/8"	3-1/2"	5-1/2"	15-29/32"	5-9/64"
EAC-10	4"	5-7/16"	14-7/8"	4"	5-1/2"	15-29/32"	5-9/64"

