



EBSEL1030A3 - EBS 10W/30V DC EL 1" Pendant

By Killark
Catalog # [EBSEL1030A3](#)

EBS 10W/30V DC EL 1" Pendant

Features

- LED Heads provide clear crisp illumination at 5000° Kelvin
- LED Head L70 value 100,000 hours for minimal maintenance
- Two head models up to 500% brighter than competitive conventional units
- Enclosure Type 4 (NEMA 4) for wet and harsh locations
- Group B is standard when using EBSHK type heads
- Automatic Safety Disconnect – Removing main cover disconnects battery power
- Ambient Suitability 0°C to 45°C Battery Unit Heads to 55°
- Compact unit requires only two mounting points
- World Voltage 120-277 VAC 50/60Hz input Other Features
- High % of lumens maintained during 90 minute egress cycle
- EBSHK type heads are fully adjustable on unit or remote when ordered with RFSL Factory Sealed mounting kits
- EBSEL type heads are factory sealed on their EZ type mounting boxes
- Heads can be remote mounted over 300' from battery unit
- Ni-Cad sealed batteries provide 90 minutes of illumination
- Integral base unit LED pilot light indicates AC power is present
- Choice of Integral or Remote Push-To-Test station to verify system operation
- Vapor Capsule to inhibit corrosion is standard with main enclosure unit
- Terminal Blocks identified for incoming and outgoing connections

Specifications

- | | |
|---------------------|---|
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups C, D• Class I, Zones 1 & 2, Groups IIB, IIA |
|---------------------|---|



EU RoHS Indicator
Buy America(n) Qualified

Current

Frequency Rating	50/60 Hz
Lumens Per Watt	108.1
Wattage	10 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	1"
----------	----

General

Series	EBS Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Optic Type	Glass Globe - Clear
UPC	783936083223
Light Source	LED
Mounting Type	Pendant

Operational

Lumens	1081
Lumen Range	0-2,000 lm

Product Assets

[Catalog \[English\]](#)

- Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer
Contact Manufacturer