



ESXR240AA2 CEN - 240V Red Strobe, 3/4" Pendant, ATEX Rated

By Killark
Catalog # [ESXR240AA2 CEN](#)

240V Red Strobe, 3/4" Pendant, ATEX Rated

Features

- Electronic component temperature range -40°C to +55°C
- NEC temperature code, T6 (<85°C)
- Flash rate-85 flashes per minute
- Xenon type lamp
- Voltage and amperage: 12-74 VDC: Draws 1.25A avg. @ 12 VDC tapering to 0.2A avg. @ 74 VDC, .75A avg. @ 24 VDC
- 120 VAC (50/60 HZ): Draws 0.30A avg.
- 240 VAC (50/60 HZ): Draws 0.17A avg.
- Power supply output: 13 watts standard 11 watts for 12-74 VDC

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Voltage Rating	240 VAC

Dimensions

Hub Size	3/4"
----------	------

General

Series	ESX Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Flashing
Optic Type	Glass Globe - Red
UPC	783936028620
Light Source	Xenon
Mounting Type	Pendant

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)

