



## CAST DEVICE BOXES • STANDARD AND HOSTILE LOCATIONS



FRS Type



FST Type

UL Standard: 514A  
 CSA Standard: C22.2 No. 18  
 Fed Spec: W-C-586D  
 NEMA: FB-1

LISTED File No. E 3397

Certified File No. LR11852

### FEATURES-SPECIFICATIONS

#### Applications

- Accommodates wiring devices and provides opening to splice, tap, or pull conductors
- Provide access to conductors for maintenance and future system changes

#### Features

- Tapered threads (NPT with integral bushings)
- Internal grounding screw
- Suitable for use in wet locations when used with gasket covers
- Cast iron is suitable for concrete use
- For use with FS-style covers see pages F41-F43
- To order without mounting lugs, contact factory

#### Material/Finish

**Copper-free Aluminum**  
 (less than 4/10 of 1%)

- Electrostatically applied powder coating


#### Duraloy Iron

- Tri-coat finish of electrozinc, chromate sealant, and electrostatically applied powder coating


FRS TYPE CAST DEVICE BOX – SHALLOW											
CATALOG NUMBER	KILLARK ALUM.	DURALOY IRON	HUB SIZE	DIMENSIONS						VOLUME CU. IN.	
				A	B	C	D	E	F		G
FRS-1	FRS-1M	FRS-1M	1/2"	7/8" (22)	2" (51)	11/16" (17)	4-5/8" (117)	2-7/8" (73)	2-1/8" (54)	—	18.0
FRS-2	FRS-2M	FRS-2M	3/4"	7/8" (22)	2" (51)	11/16" (17)	4-5/8" (117)	2-7/8" (73)	2-1/8" (54)	—	18.0

FST TYPE CAST DEVICE BOX – SHALLOW											
CATALOG NUMBER	KILLARK ALUM.	DURALOY IRON	HUB SIZE	DIMENSIONS						VOLUME CU. IN.	
				A	B	C	D	E	F		G
FST-1	FST-1M	FST-1M	1/2"	7/8" (22)	2" (51)	11/16" (17)	4-5/8" (117)	2-7/8" (73)	2-1/8" (54)	—	18.0
FST-2	FST-2M	FST-2M	3/4"	7/8" (22)	2" (51)	11/16" (17)	4-5/8" (117)	2-7/8" (73)	2-1/8" (54)	—	18.0

#### Dimensions



FRS



FST