



FXS Series - Dead-End Ground Fault Interrupter Unit - Factory Sealed - Hub Size 3/4 Inch - 20A/120Vac/60Hz - 4-6 Miliamp Trip Setting

By Killark
Catalog # [FXS-GFI-2020](#)

FXS Series - Aluminum Dead-End Ground Fault Interrupter Unit - Factory Sealed - Hub Size 3/4 Inch - 20A/120Vac/60Hz - 4-6 Miliamp Trip Setting

Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splice box.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

FXS ground fault interrupters are designed to interrupt a circuit when a ground fault is detected on equipment which may be handled by personnel in hazardous locations.

Specifications

Hazardous Rating(s)	<ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
UL File Number	E53360, E10501



CSA File Number	LR11712
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Poles	2
-----------------	---

Configuration

Back Box Type	FXB
---------------	-----

Current

Amperage Rating	20 A
Frequency Rating	50/60 Hz

Dimensions

Gross Weight with Packaging	5
Depth	5-1/8 in

General

Type	Aluminum Factory Sealed Ground Fault Interrupter
Series	FXS-GFI Series
UPC	783936198385
Color	Gray

Operational

Action	Push buttons
Actuator	Gound Fault Interupter

Product Assets

[Catalog \[English\]](#)