



GCBB-100 - GCBB Handle Replacement

By Killark
Catalog # GCBB-100

GCBB Handle Replacement

Features


- Compact rectangular enclosure with threaded cover allows easy access.
- Provided with two 3/4"-14 NPT drilled and tapped conduit openings, one top and two bottom.
- Eaton (Cutler-Hammer) Type QC Quicklag Circuit Breakers (These assemblies include the breaker as indicated).
- Push pull handle mechanism operates circuit breakers.
- Handle mechanism supplied as standard with "Lockout" in OFF position.
- Enclosures are made from copper free cast aluminum alloy (less than 4/10 of 1%).
- Special combinations of breaker amperage are available, consult factory for details.

Application

Indoor and outdoor hazardous areas where flammable gases or vapors, combustile dusts, or easily ignitable fibers or flyings may be present. Provides overcurrent and short circuit protection of branch lighting, heating, and appliance circuits.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3R, 7(B, C, D), 9(E, F, G)
UL File Number	E83969



Buy America(n) Qualified Contact Manufacturer

Conductor

Number Of Poles 4

Current

Frequency Rating 60 Hz

Dimensions

Depth 6.625 in
Width 8.125 in
Weight 12 lb.
Height 6.875 in

General

Type Replacement Handle
Enclosure Type Threaded
Series GCBB Series
Material Aluminum, Copper Free (less than 4/10 of 1%)
UPC 783936204963
Mounting Type Wall

Operational

Operating Temperature Celcius 40 Degree
Max
Actuator Handle

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)