



316 Stainless Steel Drain, 3/4" NPT - Ex e Class I Div. 2 IP66/4X with Locknut

By Killark
Catalog # [KDES60075](#)

316 Stainless Steel Drain, 3/4" NPT - Ex e Class I Div. 2 IP66/4X with Locknut

Features

- Silicone O-ring supplied as standard and suitable for use in a -55°C to +80°C temperature range.
- 316 stainless steel.
- Internal 316 stainless steel locknut supplied as standard.
- When tightened to the proper torque the joint makes a hose down tight seal for type 4, 4X & IP66 application.

Application

When installed in the bottom of a thin wall enclosure the KDE allows water from condensation to drain continuously out of the enclosure. The drain breathers are installed through clearance holes and held secured with a internal locknut. The silicone external o ring makes a hose down tight seal.

Specifications

Hazardous Rating(s)	• Class I, Divisions 2, Groups A, B, C, D • Class I, Zones 1 & 2 • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IECEx File Number	15.0002X
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X
CSA File Number	2715851



Buy America(n) Qualified	Contact Manufacturer
ATEX File Number	15ATEX3028X

Dimensions

Hub Size	3/4"
----------	------

General

Type	Drain & Breather
Series	KDE Series
Material	316 Stainless Steel
UPC	783936124049

Logistics

Carton Quantity	5
-----------------	---

Operational

Operating Temperature Range	-55°C to 80°C
Celcius	
Operating Temperature Celcius	80
Max	
Operating Temperature Celcius	-55 °C
Min	

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English, Portuguese\]](#)