



Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
NEMA 3

UL Complies: UL 844; UL 1570, UL924 (File E162407)
 UL Wet Location Listed (Indoor & Outdoor)
 Rated for 40C° ambient. Minimum start 0° C
 Temperature codes:
 Class I C,D **T6**;
 Class II E,F,G **T4**;
SP Suitable for Class III
 Certified File LR11713

FEATURES-SPECIFICATIONS

HOSTILE/LITE® E EMERGENCY

Applications

HOSTILE/LITE® EEQ Emergency Lighting fixtures provide continuous illumination under normal power and switch to emergency battery backup during power outages. Emergency Units ONLY are available that operate only when normal power fails.

Units contain battery unit that provides the OSHA required 90 minutes of illumination (same lamp) for egress.

Units are designed for general and task lighting indoors or outdoors where flammable gases or vapors or combustible dusts exist and create a hazardous location, as defined by the NEC.

See Page L212 for available Push-To-Test hazardous location control stations.


Features

- Quad-Pin long-life triple-tube compact fluorescent lamps included
- Choice of Pendant, Ceiling, Wall or Stanchion mount
- Factory Sealed - No external seal required
- Corrosion resistant-Copper-free aluminum (less than 4/10 of 1%) die-cast construction w/Baked-on epoxy/polyester powder finish
- Exposed hardware is 316 grade stainless steel
- LED charging indicator light visible through lens

Accessories

Exit sign: Model **HEXA-100** (note omit 2nd "G" in catalog number for globe-only fixture) see page L144.

Reflectors: Use standard dome **ERSD15** or angle model **ERA15** (see page L146).



EEQ 26, 32 & 42WATT NORMAL & EMERGENCY MODE FIXTURES

QUAD-PIN FLUOR. LAMP INCLUDED	LINE VOLTAGE @ 60 HZ	CATALOG NUMBER ③④⑥			
		PENDANT 3/4" ①	CEILING 3/4" ①	BRACKET 3/4" ①	STANCHION 1-1/4" ②
26Watt	120 or 277VAC⑤	EEQ2626E10A2GG	EEQ2626E10X2GG	EEQ2626E10B2GG	EEQ2626E10D4GG
32Watt	120 or 277VAC⑤	EEQ3232E10A2GG	EEQ3232E10X2GG	EEQ3232E10B2GG	EEQ3232E10D4GG
42Watt	120 or 277VAC⑤	EEQ4242E10A2GG	EEQ4242E10X2GG	EEQ4242E10B2GG	EEQ4242E10D4GG

EEQ 26, 32 & 42WATT EMERGENCY-ONLY MODE FIXTURES

QUAD-PIN FLUOR. LAMP INCLUDED	LINE VOLTAGE @ 60 HZ	CATALOG NUMBER ③④⑥			
		PENDANT 3/4" ①	CEILING 3/4" ①	BRACKET 3/4" ①	STANCHION 1-1/4" ②
26Watt	120 or 277VAC⑤	EEQ0026E10A2GG	EEQ0026E10X2GG	EEQ0026E10B2GG	EEQ0026E10D4GG
32Watt	120 or 277VAC⑤	EEQ0032E10A2GG	EEQ0032E10X2GG	EEQ0032E10B2GG	EEQ0032E10D4GG
42Watt	120 or 277VAC⑤	EEQ0042E10A2GG	EEQ0042E10X2GG	EEQ0042E10B2GG	EEQ0042E10D4GG

① Pendant, Ceiling & Bracket models may be changed to 1" hubs by changing the 12th character from 2 to 3; e.g. EEQ2626E10A3GG.

② Stanchion fixtures are 1-1/2" with a 1-1/2 to 1-1/4" reducer.

③ Omit 2nd "G" for globe-only fixture for use with HEXA-100 Exit Accessory.

④ Standard color for fixtures is Killark beige. Add -R for RED adder..

⑤ All EEQ fixtures are factory set to 120V and can be changed to 277V in field by following included instructions. Replacement battery pack kit KFBP9.

⑥ EEQ fixtures use a tank extension ring and are 2-1/2" taller than EBF fixtures (see page L143).

⑦ Photometric characteristics similar to EBF26 page L152, except adjusted for lumen output.

LUMEN OUTPUT⑦		
LAMP SOURCE	NORMAL POWER	EMERG. POWER
26Watt	1800	450
32Watt	2400	575
42Watt	3200	750

BALLAST DATA

LAMP WATTS	VOLTAGE	OPERATING AMPS	INPUT WATTS	BALLAST CIRCUIT	REGULATION
26Watt (1x26)	120 / 277 VAC	.24@120V / .11 @277V	29	HPF	Electronic
32Watt (1X32)	120 / 277 VAC	.31@120V / .13 @277V	36	HPF	Electronic
42Watt (1x42)	122 / 277 VAC	.38@120V / .17 @277V	46	HPF	Electronic



KILLARK®