



**GO8-2A3F20D N34 - G Series, AL Long
Maint. Contact 2-Pos Keyed Selector
Switch Op, Keyed Diff w/ Key Removal
Both Pos, Off-On/Blank Nameplate,
1NO/1NC**

By Killark

Catalog # [GO8-2A3F20D N34](#)

G Series - Aluminum Long Maintained Contact 2-Position Keyed
Selector Switch Operator - Keyed Different With Key Removal In
Both Positions - "Off - On"/Blank Nameplate - 1NO/1NC Contact
Rating



Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread.
- Control stations can be grouped into a single assembly thus reducing installation time and cost.

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X
UL File Number	E12379
CSA File Number	LR11714
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Poles	1
-----------------	---

Current

Contact Rating	• 60A INRUSH @ 120 VAC • 30A INRUSH @ 240 VAC • 15A INRUSH @ 480 VAC • 12A INRUSH @ 600 VAC • 0.55A INRUSH @ 125 VDC
----------------	--

Amperage Rating	10 A
Frequency Rating	50/60 Hz
Dimensions	
Gross Weight with Packaging	1
Width	2.25 in
Height	1.25 in
Length	6.31 in
Dimensions	6.31 in x 2.25 in x 1.25 in
General	
Type	Selector Switch
Series	GO Series
UPC	783936399362
Color	Black
Operational	
Action	Rotary
Actuator	2 Position Selector Switch

Product Assets

[Catalog \[English\]](#)

