



# HKH Series 20A Factory Sealed E-Stop - NC Contact - Panel Mount

By Killark  
Catalog # [HKH1NC20PE](#)

HKH 20A Factory Sealed E-Stop - NC Contact - Panel Mount

## Features


- Explosion Protected Panel Mount ESTOP contact block  
690VAC N.O. & N.C. capable of 20 Amps for Switching Duty  
and HP Ratings up to 1HP.

## Application

Contact block shall be installed in a Class I, Zone 1, AEx e II/Ex e IIC increased safety enclosure with a minimum IP54 rating or a Class I, Zone 1, AEx d IIC/Zone 21, Aex tb minimum IP64 rating, where the suitability is determined in the end application.

## Specifications

|                          |                                                                                                                         |
|--------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>Class I, Division 2, Groups A, B, C, D</li><li>Class I, Zones 1 &amp; 2</li></ul> |
| IECEx File Number        | 12.0033U                                                                                                                |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                    |
| UL File Number           | E12379                                                                                                                  |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                    |
| ATEX File Number         | 1202251U                                                                                                                |



## Current

|                  |                |
|------------------|----------------|
| Amperage Rating  | 20 A           |
| Frequency Rating | 50/60 Hz       |
| Voltage Rating   | 24-690 AC/DC V |

## General

|        |              |
|--------|--------------|
| Series | HKH Series   |
| UPC    | 783936124148 |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 20 |
|-----------------|----|

## Operational

|                                     |               |
|-------------------------------------|---------------|
| Operating Temperature Range Celcius | -40°C to 55°C |
| Action                              | Momentary     |
| Horsepower - Maximum                | 1             |

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)