



C1D1 FLOOD – INTRODUCTION & LOGIC

**PETROBRIGHT® LED****FEATURES-SPECIFICATIONS****Applications**

LED KF1L Series Explosion-proof Floods are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4X areas where wind, water, snow or high ambients can be expected. They can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC.

Typical applications include manufacturing plants, and certain chemical and petrochemical processing facilities, sewage treatment plants, off-shore and dockside installations, garages and storage facilities

Compliances

- UL-8750 for LED lighting
- ANSI/UL 1598A
- UL-844 Standard for lighting fixtures for hazardous locations, Class I, Division 1; Class II, Division 1; Class III
- CSA C22.2 no. 137-M1981 electric luminaires for use in hazardous locations
- Zone 1 and Zone 21 to IEC 60079-0, 60079-1, 60079-31, 60079-7 Standards
- Enclosed and gasketed
- NEMA 3, 4X
- IP66

Materials

- Body, end caps and lens frame corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware - stainless steel
- Thermal shock and impact resistant extra heavy-duty glass lens
- High temperature silicone gasketing
- Trunnion heavy gauge 316 SS

**LED Flood Features and Standards**

Supplemental **20KA/10KV Surge Protection** is **standard** (for 120-277 VAC models)
10KA/10KV Surge Protection (for 347-480 VAC)

- **Factory Sealed Construction**
- One 3/4" NPT & one M20 entry standard (see logic for other choices)
- Crisp White Light for Excellent Color Rendering – Chromaticity 5000 K (CCT); approx. 70 CRI
- Energy Savings – High lumens per watt
- Long Life – 100,000+ maintenance free hours to 70% initial lumens
- Instant On – Including after power interruption
- World Voltage 120 – 277VAC 50/60Hz
- Solder-LESS LED Board Connections – Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values – Industry Nomenclature for Hours of use to 70% of initial Lumens – TM-21 & calculated

Class I, Div. 1&2, Groups B,C,D
Class I, Zone 1&2, Groups IIB+H2, IIA
Class II, Div. 1&2, Groups EFG, Class III
Enclosure Type 4X, IP66 (-50°C to +55°C)

CS US File LR11713

IEC Ex Rated model (w/IEX or IEX4B suffix) Zone 1, Zone 21

Ex de IIB+H2 T6..T5, Gb, IP66

Tamb -20°C ≤ Ta ≤ +55°C; Option LT for -50°C ≤ Ta ≤ +55°C ①

Ex de IIB T6..T5, Gb, -50°C ≤ Ta ≤ +55°C ①

Ex tb IIIC T90°C Db, -50°C ≤ Ta ≤ +55°C ①

IECEx Certificate
CSA 14.0010

ATEX Certificate
SIRA14ATEX1159X

Patent Pending
Fixture
Design



KF1L with KFS-6
Slipfitter mount
on 2" pipe



Dark Sky Visor
KF1L-DARK

Suitable for Paint
Spray

Catalog Number Logic

		KF1L	125	30	XX
KF1L - Series Constant					
Fixture Wattage					
090 - 90W	150 - 150W				
105 - 105W	165 - 165W				
110 - 110W	195 - 195W				
125 - 125W					
Voltage					
30 - 120 - 277VAC 50/60Hz					
33 - 347 - 480VAC 60Hz (90W-125W)					
34 - 120-250VDC (90W-125W)					
Options					
IEX4B - Four bolt termination cover (see Note 1)					
LT - For -50°C to +55°C, IEC Zone 1 (see Note 1)					
F - Single Fuse					
FF - Double Fuse②					
D20 - Dual M-20 Entries					
D25 - Dual M-25 Entries					
D75 - Dual 3/4" NPT					

① **Construction/Certification**
 Notes: KF1L units are standard with one 3/4" NPT hub & one M20 hub – both plugged, with an 8-bolt factory sealed termination chamber, suitable for CID1 BCD -50°C to +55°C and IEC Zone 1
 Ex de suitable for -20°C to 55°C.

Use option LT for models needing IEC Zone 1, -50°C to +55°C suitability for hydrogen.

Option IEX4B utilizes 4 terminal cover bolts for Ex de and maintains all ratings EXCEPT CID1 BCD.

See logic for other entry options

② Fusing not for Canadian or Marine Installations



KF1L SERIES

C1D1 FLOOD – ORDERING & TECHNICAL DATA

ORDERING INFORMATION AND AMBIENT SUITABILITY						C1D1		C2D1		IEC ZONE 1		IEC ZONE 21		L70	
CATALOG NO.	WEIGHT LBS./KG	WATTS	VOLTAGE	AMPS	DELIVERED LUMENS	40°C	55°C	40°C	55°C	40°C	55°C	40°C	55°C	TM-21	CALCULATED
KF1L09030	46.00 / 20.87	90	120-277VAC	0.72-0.31	7182	T6	T6	(EFG)	⑥	T6	T5	160-75	175-90	60100	270000
KF1L09033			347-480VAC	0.25-0.18											
KF1L09034			120-250VDC	0.72-0.28											
KF1L10530		105	120-277VAC	0.85-0.37	8362	T6	T6	(EFG)	⑥	T6	T5	160-76	175-91	60100	270000
KF1L10533			347-480VAC	0.29-0.21											
KF1L10534			120-250VDC	0.85-0.33											
KF1L11030		110	120-277VAC	0.95-0.41	10590	T6	T6	(EFG)	⑥	T6	T5	160-77	175-92	72600	278000
KF1L11033			347-480VAC	0.33-0.24											
KF1L11034			120-250VDC	0.95-0.37											
KF1L12530		125	120-277VAC	1.10-0.48	11590	T6	T6	(EFG)	⑥	T6	T5	160-78	175-93	72600	278000
KF1L12533			347-480VAC	0.38-0.28											
KF1L12534			120-250VDC	1.10-0.43											
KF1L15030		150	120-277VAC	1.25-0.54	13280	T5	-	-	-	T5	-	-	-	60300	190000
KF1L16530		165	120-277VAC	1.38-0.60	13760	T5	-	-	-	T5	-	-	-	72600	278000
KF1L19530		195	120-277VAC	1.63-0.70	15707	T5	-	-	-	T5	-	-	-	72600	278000

① Yellow highlighted models have extra high lumen LED's.

② See logic for 347-480V availability


③ Amperage measured at 120VAC; 277VAC calculated

④ Use minimum 75° Supply Wire @40°C Ambient; 90°@55°C Ambient

⑤ C1D1 40°/55° & C2D1 40°C use Aiming Figure "A" below.

⑥ 55°C C2D1 EFG T3C Aiming Figure "B"; 55° C2D1 EF T3A Aiming Figure "A"

⑦ First number is lens temperature under 25mm layer of dust; Second number is lens temp for dust cloud.



KFL MOUNTS AND ACCESSORIES①	
CATALOG NUMBER	DESCRIPTION
KFS-6	Steel Slipfitter for 2" Pipe (2-3/8" o.d.) Tenon. Slips 3.75" Over Pipe.
KFCB	Heavy Duty Cast-Iron Crossarm Fitting for Horizontal Trunnion
KFWB	Heavy Duty Wall Mount and/or Pipe Clamp Fitting Clamps 2" Pipe (2-3/8" o.d.) Through 2-1/2" Pipe (2-7/8" o.d.)
K4040	Heavy Duty Steel Wall Bracket. (Must be with KFCB Crossarm Fitting).
4041	Heavy Duty Steel Wall Bracket 2" Pipe (2-3/8" o.d.) Tenon Fitting.
KFLG	Wire Guard, 316 Stainless Steel
VMS-C10	10' Stainless Steel Safety Cable with loop grip②
KF1L-DARK	Dark Sky Visor, White Painted Aluminum③
KF1L-DOOR	Replacement Door and Lens Assembly
KFL-STND	8 Foot Extendable Portable Stand

① Fittings available to adapt trunnion mount floodlights to crossarms, poles and walls. Must be ordered separately.

② Drop limit 1'. Attaches to luminaire cable provision and to mounting structure.

③ Designed to eliminate uplight when aimed at 45°.

Dimensions

