



C1D2 FLOOD – INTRODUCTION & LOGIC

**PETROBRIGHT® LED****FEATURES-SPECIFICATIONS****Applications**

LED Floods are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4X areas where wind, water, snow or high ambients can be expected. They can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC.

Typical applications include manufacturing plants, and certain chemical and petrochemical processing facilities, sewage treatment plants, off-shore and dockside installations, garages and storage facilities.

Compliances

- UL-8750 for LED lighting
- ANSI/UL 1598(A)
- UL-844 Standard for lighting fixtures for hazardous locations, Class I, Division 2; Class II, Divisions 1 and 2; Class III
- CSA C22.2 no. 137-M1981 electric luminaires for use in hazardous locations
- Enclosed and gasketed
- NEMA 3, 4X
- IP66

Materials

- Body and lens frame corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection
- All external hardware – stainless steel
- Thermal shock and impact resistant glass lens (Polycarbonate available)
- High temperature silicone gasketing
- Trunnion heavy gauge 316 stainless steel

LED Flood Features and Standards

Supplemental **20KA/10KV Surge Protection** is **standard** (for 120-277 VAC models)
10KA/10KV Surge Protection (for 347-480 VAC)

- Crisp White Light for Excellent Color Rendering – Chromaticity 5000K (CCT); approx. 70 CRI
- Energy Savings – High lumens per watt
- Long Life – to 100,000+ maintenance free hours to 70% initial lumens
- Ambient suitability -40°C to 55°C up to 500W^② to -50°C for non-hazardous applications
- Instant On – Including after power interruption
- World Voltage 120 – 277VAC 50/60Hz
- Solder-LESS LED Board Connections – Vibration Resistant
- LM80-08* Measurement of lumen maintenance for LED light sources

Class I, Div. 2, Groups A, B, C, D
 Class I, Zone 2, IIC, IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 Suitable for wet locations
 Marine Rated (US only)
 NEMA 3, 4X
 IP66

IEC Ex Rated Model (w/ IEX suffix)
 Zone 2 and Zone 21 areas
 Ex nA IIC T6...T3, Gc
 Ex tb IIC T105°C Db
 Tamb -50°C ≤ Ta ≤ +55°C, IP66

IECEX Certificate
 QPS 15.0011



ATEX Certificate
 CML 15ATEX4079X (nA)
 &
 CML 15ATEX3080X (tb)


PATENTED LENS and REFLECTOR DESIGN

Dark Sky Visor
 KFLH-DARK



- LM79-08* Certified “Absolute” Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values – Industry Nomenclature for Hours of use to 70% of initial Lumens – TM-21* & Calculated

* LM-xx & TM-xx are Illumination Engineering Society Standards designed to promote uniformity in testing procedures among test labs and manufacturers. For more information go to www.ies.org

Catalog Number Logic**PL - Polycarbonate Lens**

F - Single Fuse①

FF - Double Fuse①

TBL - Terminal Blocks **Looping**

P1 - 120V Photocell, factory installed

P2 - 208V-277V Photocell, factory installed

P3 - 347V Photocell, factory installed

QD - Quick Disconnect

D20 - 2x M20 entries

IEX - IEXEx includes TBL & External ground

① Fusing not for Canadian or Marine Installations

② 347V-480V +40°C Max




KFL2H SERIES

KILLARK

C1D2 FLOOD – ORDERING INFORMATION & TECHNICAL DATA

ORDERING INFORMATION AND AMBIENT SUITABILITY						C1D2 (C1Z2)		C1D2 SIMULTANEOUS		C2D1		L70	
CATALOG NO.	WEIGHT LBS./KG	WATTS	VOLTAGE	AMPS	DELIVERED LUMENS	40°C	55°C	40°C	55°C	40°C	55°C	TM-21	CALCULATED
KFL2H34030	50.00 / 22.6	340	120-277VAC	2.92-1.26	43240	T4A (T4)	T4	T4	T3C	T4	T3C	72600	278000
KFL2H34033			347-480VAC	1.02-0.72			-		-		-		
KFL2H34034			120-250VDC	2.92-1.12			T4		T3C		T3C		
KFL2H42030		420	120-277VAC	3.50-1.50	42440	T4A (T4)	T4	T4	T3C	T4	T3C	60100	270000
KFL2H42033			347-480VAC	1.22-0.86			-		-		-		
KFL2H42034			120-250VDC	3.50-1.36			T4		T3C		T3C		
KFL2H44030		440	120-277VAC	3.76-1.62	53940	T4A (T4)	T4	T4	T3C	T4	T3C	72600	278000
KFL2H44033			347-480VAC	1.30-0.94			-		-		-		
KFL2H44034			120-250VDC	3.76-1.46			T4		T3C		T3C		
KFL2H50030		500	120-277VAC	4.34-1.88	69410	T4A (T4)	T4	T4	T3C	T4	T3C	72600	278000
KFL2H50033			347-480VAC	1.50-1.08									
KFL2H50034		600	120-250VDC	4.34-1.70	74060	T4A (T4)	T4	-	-	-	-	60300	107000
KFL2H60030			120-277VAC	4.96-2.14									
KFL2H78030		780	120-277VAC	6.60-2.86	80820	T4A (T4)	T4	-	-	-	-	60300	190000

- ① Cat. Nos. are 120 through 277VAC 50/60Hz; see logic for 347-480V or 125-250VDC input
- ② Amperage measured at 120VAC; 277VAC calculated
- ③ Extra High Lumens per Watt LED Models
- ④ Use 75°C Supply Wire @ 40°C Ambient; 90°C Wire @ 55°C Ambient
- ⑤ 55°C only for 340W through 500W at 120-277VAC 50/60Hz or 125-250VDC; not 480VAC
- ⑥ For Dust Applications, limit aiming angle between 120° and -120° to minimize buildup - see figure at right
- ⑦ L70 is time in hours to 70% of initial lumens remaining. TM-21 based values require very long duration testing and is denoted "official reported" and is based on at least 6,000 minimum, to 12,000 hours testing (at time of printing). "Calculated" values by the major chip vendors utilized predict L70 life up to 278,000 hours.



KFL2H MOUNTS AND ACCESSORIES①

CATALOG NUMBER	DESCRIPTION
KFS-6	Steel Slipfitter for 2" Pipe (2-3/8" o.d.) Tenon. Slips 3.75" Over Pipe.
KFCB	Heavy Duty Cast-Iron Crossarm Fitting for Horizontal Trunnion
KFWB	Heavy Duty Wall Mount and/or Pipe Clamp Fitting Clamps 2" Pipe (2-3/8" o.d.) Through 2-1/2" Pipe (2-7/8" o.d.)
K4040	Heavy Duty Steel Wall Bracket. (Must be with KFCB Crossarm Fitting).
4041	Heavy Duty Steel Wall Bracket 2" Pipe (2-3/8" o.d.) Tenon Fitting. Use with KFS-6.
KFLG	Wire Guard, 316 Stainless Steel (order 4 per fixture)
VMSC10②	10' Stainless Steel Safety Cable with loop grip
KFLH-DARK③	Dark Sky Visor, White Painted Aluminum
KFLH-DOOR	Replacement Internal Reflector and Lens Assembly (order 4 per fixture as required)

- ① Fittings available to adapt trunnion mount floodlights to crossarms, poles and walls. Must be ordered separately.
- ② Drop limit 1'. Attaches to luminaire cable provision and to mounting structure.
- ③ Designed to eliminate uplight when aimed at 45°.

