

# FITTINGS

O SERIES / DURALOY® 5 SERIES



## ALUMINUM OR MALLEABLE IRON CONDUIT BODIES



C Type



E Type

- Suitable for wet locations when used with gasketed covers.
- Federal Specification W-C-586D/A-A 50563.
- Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b), Class 1, Div. 2, (Suitable for use in Class 1 Zone 2 applications) 502.10 and 503.10.

UL LISTED File No. E3397

SP Certified File No. LR11852

### FEATURES-SPECIFICATIONS

**DURALOY<sup>5</sup>**

#### Applications

To provide access to conductors for pulling, splicing, and maintenance. Threaded for rigid conduit and IMC.

#### Features

- Tapered threaded hubs (NPT)
- Raintight when used with gasketed covers
- Malleable iron suitable for use in concrete
- Interchangeable with competitive products
- Stainless steel screws on stamped and cast covers

#### Material/Finish

**Copper-free Aluminum**  
(less than 4/10 of 1%)

- Electrostatically applied powder coating

#### Duraloy Malleable Iron

- Tri-coat finish of electrozinc, chromate sealant, and electrostatically applied powder coating.

| C TYPE CONDUIT BODY* |              |          |                  |                 |                 |                  |                   |   |                  |                |
|----------------------|--------------|----------|------------------|-----------------|-----------------|------------------|-------------------|---|------------------|----------------|
| CATALOG NUMBER       |              | HUB SIZE | DIMENSIONS       |                 |                 |                  |                   |   |                  | VOLUME CU. IN. |
| KILLARK ALUM.        | DURALOY IRON |          | A                | B               | C               | D                | E                 | F | G                |                |
| OC-1                 | OC-1M        | 1/2"     | 5-3/16"<br>(132) | 1-3/8"<br>(35)  | 1-3/8"<br>(35)  | 1"<br>(25)       | 3-5/32"<br>(80)   | — | 5/8"<br>(16)     | 4.0            |
| OC-2                 | OC-2M        | 3/4"     | 6-1/8"<br>(156)  | 1-5/8"<br>(41)  | 1-5/8"<br>(67)  | 1-7/32"<br>(31)  | 3-25/32"<br>(96)  | — | 3/4"<br>(19)     | 7.0            |
| OC-3                 | OC-3M        | 1"       | 7-1/8"<br>(181)  | 2"<br>(51)      | 1-7/8"<br>(48)  | 1-15/32"<br>(37) | 4-17/32"<br>(115) | — | 15/16"<br>(24)   | 12.0           |
| OC-4                 | OC-4M        | 1-1/4"   | 9-1/8"<br>(232)  | 2-5/8"<br>(67)  | 2-5/8"<br>(67)  | 2"<br>(51)       | 6"<br>(152)       | — | 1-3/16"<br>(30)  | 32.0           |
| OC-5                 | OC-5M        | 1-1/2"   | 9-1/4"<br>(235)  | 2-3/4"<br>(70)  | 2-5/8"<br>(67)  | 2"<br>(51)       | 6"<br>(152)       | — | 1-3/8"<br>(32)   | 36.0           |
| OC-6                 | OC-6M        | 2"       | 11-7/8"<br>(302) | 3-1/2"<br>(89)  | 3-1/8"<br>(79)  | 2-9/16"<br>(65)  | 8-1/16"<br>(205)  | — | 1-5/8"<br>(38)   | 70.0           |
| OC-7                 | OC-7M        | 2-1/2"   | 15-1/8"<br>(384) | 4"<br>(102)     | 4-3/8"<br>(111) | 3-11/16"<br>(94) | 10-5/8"<br>(270)  | — | 1-13/16"<br>(54) | 153.0          |
| OC-8                 | OC-8M        | 3"       | 15-1/8"<br>(384) | 4-3/4"<br>(121) | 4-3/8"<br>(111) | 3-11/16"<br>(94) | 10-5/8"<br>(270)  | — | 2-3/16"<br>(54)  | 181.0          |
| OC-9                 | OC-9M        | 3-1/2"   | 18-3/8"<br>(467) | 5-1/2"<br>(140) | 5-1/2"<br>(140) | 4-7/8"<br>(124)  | 13-1/8"<br>(333)  | — | 2-1/2"<br>(67)   | 290.0          |
| OC-0                 | OC-0M        | 4"       | 18-3/8"<br>(467) | 5-5/8"<br>(143) | 5-1/2"<br>(140) | 4-7/8"<br>(124)  | 13-1/8"<br>(333)  | — | 2-3/4"<br>(67)   | 320.0          |

| E TYPE CONDUIT BODY* |              |          |                 |                 |                |                  |                   |   |              |                |
|----------------------|--------------|----------|-----------------|-----------------|----------------|------------------|-------------------|---|--------------|----------------|
| CATALOG NUMBER       |              | HUB SIZE | DIMENSIONS      |                 |                |                  |                   |   |              | VOLUME CU. IN. |
| KILLARK ALUM.        | DURALOY IRON |          | A               | B               | C              | D                | E                 | F | G            |                |
| OE-1                 | OE-1M        | 1/2"     | 4-5/8"<br>(117) | 1-3/8"<br>(35)  | 1-3/8"<br>(35) | 1"<br>(25)       | 3-9/32"<br>(83)   | — | 5/8"<br>(16) | 4.0            |
| OE-2                 | OE-2M        | 3/4"     | 5-3/8"<br>(41)  | 1-5/8"<br>(137) | 1-5/8"<br>(41) | 1-7/32"<br>(29)  | 3-15/16"<br>(100) | — | 3/4"<br>(19) | 7.0            |
| OE-3                 | OE-3M        | 1"       | 6-1/4"<br>(159) | 2"<br>(51)      | 1-7/8"<br>(48) | 1-15/32"<br>(35) | 4-17/32"<br>(115) | — | 7/8"<br>(22) | 12.0           |

\* For conduit body packaged with cover and gasket, add CG to the catalog number.

#### Dimensions

