



UGRA



UGMG



XHL



XHLF

FEATURES-SPECIFICATIONS

UNIVERSAL ADAPTER KIT

ACCEPTOR® receptacles are available with an adapter kit for mounting to Crouse-Hinds® EDS Series or Appleton® EFD Series back boxes.

ACCEPTOR receptacles properly installed with these adapter kits are U.L. Listed for use in Class I, Div. 2, Groups B,C,D hazardous locations and Zone II, Groups IIB + H2, IIA.

Kit contains one ACCEPTOR® receptacle plus adapter plate and mounting bolts.

UGRA ADAPTER KIT	
NEMA RATING & CONFIGURATION	ADAPTER KIT CATALOG NUMBER
20 Amp 125 Volt 2 POLE 3 WIRE 5-20R	UGRA-20231
20 Amp 250 Volt 2 POLE 3 WIRE 6-20R	UGRA-20232

Listed File No. E91049

Certified LR14667

OPTIONAL STRAIN RELIEF GRIP FOR UGP PLUGS

Kellems® Wire Mesh Grips have been specially engineered as an optional attachment for cable strain relief or bend-control. These grips are double weaved in stainless steel for exceptional strength and durability.

CATALOG NUMBER	DESCRIPTION
UGMG	Mesh grip

XHL SERIES HAND LAMPS

XHL Series Hand Lamps are a handy accessory to the ACCEPTOR® Series. Used as a supplemental illumination source for areas where flammable materials are present such as processed finished goods, storage vats, or handling areas.

Features XHL Incandescent

- Phenolic handle for long service in rugged conditions
- Aluminum guard
- Heat and impact resistant globe
- Supplied with an A-21 100 Watt (100A/RS) Rough Service lamp
- Supplied with 2 grommets for use with either 14/3 or 16/3 user furnished SO cable

CATALOG NUMBER	DESCRIPTION
XHL-100	Handlamp
XHL-GL	Replacement globe
XHLG	Replacement guard
XHLS	Replacement socket

XHL Incandescent
Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA

Listed File No. E97760

Certified File No. LR10019

Features XHLF Fluorescent

- No exposed metal parts
- Furnished with 26 watt 1800 Lumen fluorescent lamp and light shield
- Supplied with grommet for use with 16/3 user furnished SO cable

CATALOG NUMBER	DESCRIPTION
XHLF26	Fluorescent hand lamp
XHLF26-50KP	Fluorescent hand lamp with 50' of 16/3 SOW cord and 15A Acceptor plug

XHLF Fluorescent
Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB,IIA
Class II, Div. 1 & 2, Groups E,F,G

Listed File No. E97760



KILLARK®