



TWOLRL Type



TWOT Type



LISTED - FILE E3397



CERTIFIED - FILE LR11852

See files for details or call Killark.

## FEATURES-SPECIFICATIONS

## Applications

- For use with E.M.T conduit thin wall
- To make bends in the conduit system
- Connect conduit sections
- Provide access to the conduit system
- As a pulling outlet
- Provide openings for taps or splices

## Features

- Easy installation (screwdriver is only tool required)
- Complete selection of sizes and hub configurations

## Material/Finish

## Copper-free Aluminum


(less than 4/10 of 1%)

- Electrostatically applied powder coating
- Aluminum and steel/iron type 5 covers and gaskets can be used with TW series bodies. See page F23


| TWO LRL TYPE CONDUIT BODY |              |                  |                 |                 |                 |                 |                  |              |                |
|---------------------------|--------------|------------------|-----------------|-----------------|-----------------|-----------------|------------------|--------------|----------------|
| CATALOG NUMBER            | CONDUIT SIZE | A                | B               | C               | D               | E               | F                | G            | VOLUME CU. IN. |
| TWOLRL-1                  | 1/2"         | 4-1/2"<br>(114)  | 1-5/16"<br>(33) | 3-1/8"<br>(79)  | 1-1/8"<br>(29)  | 3-1/2"<br>(89)  | 2-3/16"<br>(56)  | 5/8"<br>(16) | 4.0            |
| TWOLRL-2                  | 3/4"         | 5-3/16"<br>(132) | 1-1/2"<br>(38)  | 3-3/4"<br>(95)  | 1-1/4"<br>(32)  | 4-1/8"<br>(105) | 2-5/16"<br>(59)  | 3/4"<br>(19) | 7.0            |
| TWOLRL-3                  | 1"           | 6-1/4"<br>(159)  | 1-3/4"<br>(44)  | 4-1/2"<br>(114) | 1-9/16"<br>(40) | 4-7/8"<br>(124) | 2-13/16"<br>(71) | 7/8"<br>(22) | 12.0           |

| TWO T TYPE CONDUIT BODY |          |                   |                |                 |                 |                 |   |                 |                |
|-------------------------|----------|-------------------|----------------|-----------------|-----------------|-----------------|---|-----------------|----------------|
| CATALOG NUMBER          | HUB SIZE | DIMENSIONS        |                |                 |                 |                 |   |                 | VOLUME CU. IN. |
|                         |          | A                 | B              | C               | D               | E               | F | G               |                |
| TWOT-1                  | 1/2"     | 5-3/16"<br>(132)  | 15/16"<br>(24) | 2-1/4"<br>(57)  | 1-1/8"<br>(29)  | 3-1/2"<br>(89)  | — | 5/8"<br>(16)    | 4.0            |
| TWOT-2                  | 3/4"     | 5-3/4"<br>(146)   | 1-1/2"<br>(38) | 2-5/16"<br>(59) | 1-3/16"<br>(30) | 4-1/8"<br>(105) | — | 3/4"<br>(19)    | 7.0            |
| TWOT-3                  | 1"       | 7"<br>(178)       | 1-3/4"<br>(44) | 3"<br>(76)      | 1-9/16"<br>(40) | 4-7/8"<br>(124) | — | 15/16"<br>(24)  | 12.0           |
| TWOT-4                  | 1-1/4"   | 8-11/16"<br>(221) | 2-1/2"<br>(64) | 3-1/2"<br>(89)  | 2-3/16"<br>(56) | 6-1/2"<br>(165) | — | 1-3/16"<br>(30) | 32.0           |
| TWOT-5                  | 1-1/2"   | 8-1/8"<br>(206)   | 2-1/2"<br>(64) | 3-3/8"<br>(86)  | 2-3/16"<br>(56) | 6-1/2"<br>(165) | — | 1-3/8"<br>(32)  | 36.0           |
| TWOT-6                  | 2"       | 10"<br>(254)      | 3-1/8"<br>(79) | 3-3/4"<br>(95)  | 2-3/4"<br>(70)  | 8-5/8"<br>(219) | — | 1-5/8"<br>(38)  | 70.0           |

## Dimensions



LR Type



T Type



KILLARK®