



VM3S106 - VM3 Series - 100W High Pressure Sodium 120/277/347V Housing

By Killark
Catalog # [VM3S106](#)

VM3 Series - 100W High Pressure Sodium 120/277/347V Housing



Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4” glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types.
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors.
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect.

Specifications

- | | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D |
|---------------------|--|

EU RoHS Indicator

Current

- | | |
|------------------|-----------------------|
| Frequency Rating | 60 Hz |
| Voltage Rating | Tri - 120/277/347 VAC |
| Wattage | 100 W |

General

- | | |
|---------------|--|
| Optic Type | Luminaire Only |
| Mounting Type | Luminaire Only |
| UPC | 783936966083 |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type | Powder Epoxy Paint |
| Series | VM3 Series |

Logistics

- | | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

- Class I, Zone 2, Groups IIC, IIB, IIA
 - Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer