



## VM4LB9IE230 - VM4LB 9000 Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz

By Killark

Catalog # [VM4LB9IE230](#)

VM4LB 9000 Lumen Range Standard with 2000 Lumen Battery Backup 120-277VAC 50/60 Hz

### Features

- Standard supplemental 6KV surge protection
- Optional supplementary surge protection available 20KA/10KV (120-277 VAC), 10KA/10KV (347-480 VAC)
- Traditional Industrial Appearance, Suitability, and Photometric Performance
- Wide variety of optics including globes, globes with reflectors, all-glass refractors, spin-top refractors and flat lens
- Swing-Barrel Nut patented tank mounting system
- Optional Mounting arrangements including Pendant, Wall, Ceiling, Stanchion and others
- VM4L LED Housings can be retrofitted to existing VM splice boxes to upgrade from HID sources
- Crisp White Light for Excellent Color Rendering - Chromaticity 5000 K (CCT range) approx. 70 CRI
- Energy Savings - less than 130 Watts of Power
- Long Life - 50,000 - 55,000 maintenance free hours to 70% initial lumens
- Ambient suitability -40°C to 65°C on select models
- Instant On - Including after power interruption
- World Voltage 120 - 277VAC 50/60Hz
- Solderless LED Board Connections - Vibration Resistant
- Dual Driver Option (DDR) - For additional energy savings, half of the fixture can be turned off
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)



- Two LED internal heat sink styles » Bulb VM4LB » Concave VM4LC

### Specifications

Buy America(n) Qualified  
EU RoHS Indicator

Contact Manufacturer  
Contact Manufacturer

### Current

|                 |             |
|-----------------|-------------|
| Voltage Rating  | 120-277 VAC |
| Lumens Per Watt | 149         |
| Wattage         | 65 W        |

### General

|              |                                              |
|--------------|----------------------------------------------|
| UPC          | 783936151755                                 |
| Light Source | LED                                          |
| Material     | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type  | Powder Epoxy Paint                           |
| Series       | VM4L Series                                  |

### Operational

|                             |                 |
|-----------------------------|-----------------|
| Operating Temperature Range | -20°C to +50°C  |
| Celcius                     |                 |
| Lumens                      | 9692            |
| Lumen Range                 | 5,001-10,000 lm |
| Color Temperature           | 5000 K          |

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand