



VM4P150 - VM4 Series - 150W Metal Halide Quadri-Volt Housing

By Killark
Catalog # [VM4P150](#)

VM4 Series - 150W Metal Halide Quadri-Volt Housing



Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4” glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect

Specifications

Hazardous Rating(s)		• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator		Contact Manufacturer
Current		
Frequency Rating		60 Hz
Voltage Rating		Quad - 120/277/347/480 VAC
Wattage		150 W
General		
Optic Type		Luminaire Only
Mounting Type		Luminaire Only
UPC		783936967462
Light Source		Metal Halide Pulse
Material		Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type		Powder Epoxy Paint
Series		VM4 Series