



VM5P250NR - VM5 Series, AL 250 W High Wattage Pulse Start Mtl Halide Light Fixture (w/o Lamp), Optic Thread 7-3/4", Quadri-Volt 120/208/240/277V, 60Hz

By Killark
Catalog # VM5P250NR

VM5 Series - Aluminum 250 Watt High Wattage Pulse Start Metal Halide Light Fixture (Lamp Not Included) - Optic Thread Size 7-3/4 Inch -Quadri-Volt (120/208/240/277V) At 60Hz - Restricted Breather

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4" glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect

Specifications

- Hazardous Rating(s)
- Class I, Division 2, Groups A, B, C, D



EU RoHS Indicator

Current

- Frequency Rating 60 Hz
Voltage Rating Quad - 120/277/347/480 VAC
Wattage 250 W

General

- Optic Type Luminaire Only
Lamp Type Mogul Base
Mounting Type Luminaire Only
UPC 783936967363
Light Source Metal Halide Pulse
Material Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type Powder Epoxy Paint
Series VM5 Series

- Class I, Zone 2, Groups IIC, IIB, IIA
 - Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer