



VML-X Series LED Area light 140 Watt, 120-277VAC, 18000 Lumen 1-1/4" Straight Stanchion

By Killark
Catalog # [VML2X1830S4G](#)

VML-X Series LED Area light 140 Watt, 120-277VAC, 18000 Lumen 1-1/4" Straight Stanchion

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Application

Class I Division 2 Hazardous Locations;Class II Hazardous Dust;Zone 2 Hazardous Locations;Off and On Shore Oil and Gas;Wet and Marine Locations;Food and Beverage;Heavy Industrial

Specifications

Hazardous Rating(s)	• Class I, Div2, Groups A,B,C,D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Div. 1&2, Groups E,F,G • IECEX QPS 15.0006 • Ex ec IIC T4/T3 Gc • Ex tb IIIC T4/T3 Db • QPS 22ATEX7000
---------------------	--



Current

Current / Amperage Rating	1.17-0.51 A
Frequency Rating	50-60 Hz
Wattage	140 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	1-1/4"
----------	--------

General

Optic Type	Glass Globe
Series	VML-X Series
Light Source	LED
Mounting Type	Straight Stanchion
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	18000
Lumen Range	12,000 - 18,000 lm

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)