



# VSL1330F1HG-CP - VSL Series LED Vapor Tight/ Utility, Hazardous Rated 13 Watt, 120-277 VAC 5000K, 1211 Lumens

By Killark  
Catalog # [VSL1330F1HG-CP](#)

VSL Series LED Vapor Tight/ Utility, Hazardous Rated 13 Watt, 120-277 VAC 5000K, 1211 Lumens

## Features

- Integral driver – maintains fixture’s compact profile to fit in existing spaces
- Ambient suitability -40°C to 55°C
- World Voltage 120 - 277VAC 50/60Hz
- Instant On – Including after power interruption
- Solder-LESS LED Board Connections – Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified “Absolute” Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

## Application

Killark ‘VSL’ Series LED fixtures are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4 areas where wind, water, snow or high ambients can be expected. VSL’s are sized to replace “Utility” type fixtures (incandescent or CFL’s) in hallways, closets, elevator pits, docks, stairwells, access tunnels, and mechanical rooms. These fixtures can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC. Typical applications include manufacturing plants, and certain chemical and petrochemical processing facilities, sewage treatment plants, off-shore and dockside installations, and garage areas

## Specifications

|                     |                                                                                                                                        |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class I, Zone 2, Groups IIC,IIB,IIA</li></ul> |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------|



|                          |                                     |
|--------------------------|-------------------------------------|
| EU RoHS Indicator        | • Class II, Division 2, Groups F, G |
| Buy America(n) Qualified | • Class III, Divisions 1 & 2        |
|                          | Contact Manufacturer                |
|                          | Contact Manufacturer                |

## Current

|                  |             |
|------------------|-------------|
| Current Rating   | 60 A        |
| Frequency Rating | 50/60 Hz    |
| Lumens Per Watt  | 100         |
| Wattage          | 13 W        |
| Voltage Rating   | 120-277 VAC |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 1/2" |
|----------|------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Series        | VSL Series                                   |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Optic Type    | Glass Globe - Clear                          |
| UPC           | 783936082653                                 |
| Light Source  | LED                                          |
| Mounting Type | Ceiling w/Feet & Adapter                     |

## Operational

|             |            |
|-------------|------------|
| Lumens      | 1300       |
| Lumen Range | 0-2,000 lm |

## Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)