



CERTILITE®V OPTICS & GUARDS						
DESCRIPTION	 VM1/VM3 Low Wattage 5-1/2" Optic Thread Size		 VM2/VM4/VM5QL Low Wattage 7-3/4" Optic Thread Size		 VM5 High Wattage 7-3/4" Optic Thread Size	
	OPTICS	GUARD	OPTICS	GUARD	OPTICS	GUARD
Globe (glass)	VMG17	VMAG17	VMG25	VMAG25S	VMG40	VMAG40S
Refractor (all glass) Type V	VMR175	VMAG17	VMR255	VMAG25S	—	—
Refractor (all glass) Type I	VMR171⑦	VMAG17	VMR251⑦	VMAG25S	—	—
Refractor (all glass) Type III	—	—	VMR253⑦	VMAG25S	—	—
Refractor (spin top glass) 8" Type V	VZRG1550	VMRWG8	—	—	—	—
Refractor (spin top glass) 12" Type V	VZRG2550	VMRWG	VZRG4050①	VMRWG	VZRG4050	VMRWG
Refractor (spin top glass) 12" Type II	VZRG2520	VMRWG	VZRG4020①	VMRWG	VZRG4020	VMRWG
Refractor (spin top plastic) 12" Type V	VZRP175	VMRWG	—	—	—	—
Enclosed Reflector (glass lens)	—	—	VMER40	VMERG	VMER40	VMERG
Enclosed Reflector (plastic lens)	—	—	VMEP40	—	VMEP40	—
Globe (Tuffskin® coated)⑤	VMG17F	VMAG17	VMG25F	VMAG25S	VMG40F	VMAG40S
Globe (Teflon® coated)⑤	VMG17T	VMAG17	VMG25T	VMAG25S	VMG40T	VMAG40S
Refractor (Teflon coated) Type V	VMR175T	VMAG17	VMR255T	VMAG25S	—	—
Refractor (Teflon coated) Type I	VMR171T	VMAG17	VMR251T	VMAG25S	—	—
Refractor (Teflon coated) Type III	—	—	VMR253T	VMAG25S	—	—
Refractor (Spin Top Teflon coated) 8" Type V	—	VMRWG8	—	—	—	—
Refractor (Spin Top Teflon coated) 12" Type V	VZRG2550T	VMRWG	VZRG4050T①	VMRWG	VZRG4050T	VMRWG
Refractor (Spin Top Teflon coated) 12" Type II	VZRG2520T	VMRWG	VZRG4020T①	VMRWG	VZRG4020T	VMRWG

OPTICS										
	VMG17	VMR175 VMR171	VZRG1550	VZRG2550 VZRG2520 VZRP175⑥	VMG25	VMR255 VMR253 VMR251	VMG40	VMER40	VZRG4050 VZRG4020	VMEP40⑧
GUARDS										
	VMAG17②	VMAG17②	VMRWG8④	VMRWGS③	VMAG25S③	VMAG25S③	VMAG40S③	VMERG③	VMRWG8③	

- ① For reference VM5 Spin Top optics fit VM4 tanks, but VM3 tanks and optics are recommended for low wattage Spin Top applications. VM3 12" Spin Tops ship with a mogul-to-mogul extender for improved photometrics.
- ② Standard material, copper-free aluminum painted.
- ③ Standard material, 316 stainless steel.
- ④ Standard material, plated steel.

- ⑤ Tuffskin® is a registered trademark of Thomas Manufacturing, Co. Teflon® is a registered trademark of DuPont, Inc. Alzak is a registered trademark of Alcoa.
- ⑥ 175W max; not hazloc listed
- ⑦ Type I (III) all-glass refractors align with fixture hinge. Ceiling mount unit utilizing these optics must have offset conduit feed.
- ⑧ For wall applications, mount must be spaced out.

CERTILITE®V REFLECTORS				
				
VMPSD40	VMPA40	HRD400	HRD400ALZ	VMAGBC
Standard Dome Fiberglass White Reflector Dia: 16"	30° Angle Fiberglass White Reflector Dia: 16"	Deep Aluminum White Reflector Dia: 21"	Deep Aluminum Anodized Reflector Dia: 21"	Bottom Closure for VMAG25S/VMAG40S



**DE3B | VE3B | VE3Q
DE4B | VE4B | VE4Q SERIES • LIGHTING
COMPONENTS**



Pendant



Flexible Pendant



Ceiling



Cone Top



25° Stanchion



Straight Stanchion



EZ Adapter* VMEZA

See Ordering
Information on
Page L83 for EZ
Mounting Boxes

MOUNTING SPLICE BOXES								
	CATALOG NUMBER							
HUB SIZE	PENDANT	FLEXIBLE PENDANT	CEILING 4 HUB	CEILING 5 HUB	WALL	CONE TOP	25 DEGREE STANCHION	90 DEGREE STANCHION
3/4"	VMA2B	VMF2B	VMX2B	VMX6B	VMB2B	VMC2B	—	—
1"	VMA3B	VMF3B	VMX3B	VMX7B	VMB3B	VMC3B	—	—
1-1/4"	—	—	—	—	—	—	VMD4B	VMS4B
1-1/2"	—	—	—	—	—	—	VMD5B	VMS5B
M-20	—	—	VMX8B**	VMX9B	—	—	—	—

*VMEZA is used between a ballast tank and an EZ mount-ordered separately. See L94 for more information.

**VMX8B furnished with 3 non-metallic  plugs.

OPTICS & GUARDS					
DESCRIPTION		5-1/2" Optic Thread Size		7-3/4" Optic Thread Size	
		OPTICS	GUARD	OPTICS	GUARD
Globe (glass)		VMG17	VMAG17	VMG25	VMAG25S
Refractor (all glass) Type V		VMR175	VMAG17	VMR255	VMAG25S
Refractor (all glass) Type I		VMR171	VMAG17	VMR251	VMAG25S
Refractor (all glass) Type III		—	—	VMR253	VMAG25S
Refractor (spin top glass) 8" Type V		VZRG1550	VMRWG8	—	—
Refractor (spin top glass) 12" Type V		VZRG2550	VMRWG	VZRG4050	VMRWG
Refractor (spin top glass) 12" Type II		VZRG2520	VMRWG	VZRG4020	VMRWG
Refractor (spin top plastic) 12" Type V		VZRP175	VMRWG	—	—
Enclosed Reflector (glass lens)		—	—	VMER40	VMERG
Enclosed Reflector (plastic lens)		—	—	VMEP40	—



DE3B/VE3B/VE3Q
5-1/2" Optic



DE4B/VE4B/VE4Q
7-3/4" Optic

OPTICS										
	VMG17	VMR175 VMR171	VZRG1550	VZRG2550 VZRG2520 VZRP175	VMG25	VMR255 VMR253 VMR251	VMG40	VMER40	VZRG4050 VZRG4020	VMEP40

GUARDS									
	VMAG17	VMAG17	VMRWG8	VMRWG8	VMAG25S	VMAG25S	VMAG40S	VMERG	VMRWG8

REFLECTORS				
VMPD40	VMPA40	HRD400	HRD400ALZ	
Standard Dome Fiberglass White Reflector Dia: 16"	30° Angle Fiberglass White Reflector Dia: 16"	Deep Aluminum White Reflector Dia: 21"	Deep Aluminum Anodized Reflector Dia: 21"	

VMAGBC
Bottom Closure for VMAG25S/VMAG40S