



VSL1630W1HG-CP - VSL Series LED Vapor Tight/ Utility, Hazardous Rated 16 Watt, 120-277 VAC 5000K, 1328 Lumens

By Killark
Catalog # [VSL1630W1HG-CP](#)

VSL Series LED Vapor Tight/ Utility, Hazardous Rated 16 Watt, 120-277 VAC 5000K, 1328 Lumens

Features

- Integral driver – maintains fixture’s compact profile to fit in existing spaces
- Ambient suitability -40°C to 55°C
- World Voltage 120 - 277VAC 50/60Hz
- Instant On – Including after power interruption
- Solder-LESS LED Board Connections – Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified “Absolute” Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

Application

Killark ‘VSL’ Series LED fixtures are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4 areas where wind, water, snow or high ambients can be expected. VSL’s are sized to replace “Utility” type fixtures (incandescent or CFL’s) in hallways, closets, elevator pits, docks, stairwells, access tunnels, and mechanical rooms. These fixtures can be used in locations made hazardous by the presence of flammable vapors or gases or combustible dusts as defined by the NEC. Typical applications include manufacturing plants, and certain chemical and petrochemical processing facilities, sewage treatment plants, off-shore and dockside installations, and garage areas

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC,IIB,IIA
---------------------	--



EU RoHS Indicator	• Class II, Division 2, Groups F, G
Buy America(n) Qualified	• Class III, Divisions 1 & 2
	Contact Manufacturer
	Contact Manufacturer

Current

Current Rating	60 A
Frequency Rating	50/60 Hz
Lumens Per Watt	101.6
Wattage	16 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	1/2"
----------	------

General

Series	VSL Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Optic Type	Glass Globe - Clear
UPC	783936082738
Light Source	LED
Mounting Type	Wall Bracket W/Feet

Operational

Lumens	1625
Lumen Range	0-2,000 lm

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)