



Diagonal Cutting Pliers, Insulated, High-Leverage, Angled Head, 8-Inch



These Insulated Diagonal-Cutting pliers feature two layers of insulation to protect against electric shock. Clearly marked with the official 1000V symbol, these pliers meet or exceed ASTM F1505-16 and IEC 60900:2018 standards for insulated tools. The head is angled to get into confined spaces. The high-leverage design provides 36-percent greater cutting power than other plier designs.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length (Inch):	8.24
Overall Length (cm):	20.9	Material:	Induction Hardened Steel
Nose Type:	Angled	Jaw Length (Inch):	0.813
Jaw Length (cm):	2.1	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.46
Jaw Thickness (cm):	1.2	Jaw Capacity (Inch):	1.07
Jaw Capacity (cm):	2.7	Cutting Knives:	Standard
Cut Style:	Diagonal-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length (Inch):	4.9	Handle Length (cm):	12.4
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight (oz):	11.2	Weight (g):	318