

### Features

- 0.5 gpf (1.9 lpf)
- Activation distance is factory-set
- Chloramine and chlorine resistance on all rubber components exposed to waterway
- Engineered for optimal performance with KOHLER® commercial fixtures
- 125-micron filter protects internal components
- No external flush volume adjustment ensures water conservation
- 24-hour automatic sentinel flush keeps trapway fresh
- Mechanical override enables flushometer to be used manually even during a power outage
- Powered by a 30 year/875,000 cycle hybrid energy cell, based on 72 uses per day
- Less stop valve and tailpiece
- Patented piston technology for superior flush volume accuracy

### Material

- Brass construction with durable Polished Chrome finish

### Technology

- Flushometer activates when hand is waved over electronic infrared WAVE sensor

### Installation

- Intended for urinal installations with 3/4" (19 mm) top spud coupling connection

### Recommended Products/Accessories

- 1421939 Flushometer Arm Extension Kit
- 1509698 Pressure Gauge Kit, 1/8"

### Optional Products/Accessories

- GP1118986 Flushometer Extension Kit
- K-10313 Flushometer 12" rough-in kit



ADA CSA B651 OBC

### Codes/Standards

ASME A112.18.1/CSA B125.1  
ASSE 1037/ASME A112.1037/CSA B125.37  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color                                                                               | Code | Description     |
|-------------------------------------------------------------------------------------|------|-----------------|
|  | CP   | Polished Chrome |



**Technical Information**

All product dimensions are nominal.

**Spout:**

**Pressure/fixture Supply Requirements**

|                      |                    |
|----------------------|--------------------|
| Fixture pressure     | 80 psi (551.6 kPa) |
| max (static):        |                    |
| Fixture pressure min | 25 psi (172.4 kPa) |
| (static):            |                    |
| Min flowing          | 25 psi (172.4 kPa) |
| pressure:            |                    |
| Min flow rate:       | 25 gpm (94.6 lpm)  |

**Notes**

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.