

KOHLER® Faucets

Rite-Temp® bath and shower trim with valve, 1.75 gpm
K-R72783-4G

Features

- Single lever handle allows for both on/off activation and temperature setting
- 1.75 gpm (gallons per minute) showerhead flow rate
- Rite-Temp® pressure-balancing technology maintains water temperature within +/- 3°F
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Coordinates with other products in the Elliston collection

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Heavy duty slip-fit clamp design and NPT threaded spout
- Wall-mount



Codes/Standards

ASME A112.18.1/CSA B125.1
ASSE 1016/ASME A112.1016/CSA B125.16
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

9-21-2025 08:58 - US/CA

THE BOLD LOOK
OF **KOHLER®**

KOHLER® Faucets Rite-Temp® bath and shower trim with valve, 1.75 gpm K-R72783-4G

Elliston®



Technical Information

All product dimensions are nominal.

Spout:

Spout reach: 5" (128 mm)

Shower/Rainhead rated max flow: 1.75 gal/min (6.6 l/min)

Notes

Install this product according to the installation instructions.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between the valve and the wall-mount spout.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.