

# PRODUCT INFORMATION PACKET

Model No: 096013.00

Catalog No: 096013.00

Parallel Shaft Gearmotor, 0.33 HP, 3 Ph, 60/50 Hz, 230 V, 58 RPM, 42Y Frame, TEFC



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**Nameplate Specifications**


Output HP	<b>0.33 Hp</b>	Output KW	<b>0.25 kW</b>
Frequency	<b>60/50 Hz</b>	Voltage	<b>230 V</b>
Current	<b>1.6/0.80 A</b>	Speed	<b>58 rpm</b>
Service Factor	<b>1</b>	Phase	<b>3</b>
Duty	<b>Continuous</b>	Insulation Class	<b>F</b>
KVA Code	<b>L</b>	Frame	<b>42Y</b>
Enclosure	<b>Totally Enclosed Fan Cooled</b>	Thermal Protection	<b>No Protection</b>
Ambient Temperature	<b>40 °C</b>	Drive End Bearing Size	<b>6203</b>
Opp Drive End Bearing Size	<b>6201</b>	UL	<b>Recognized</b>
CSA	<b>Y</b>	CE	<b>N</b>

**Technical Specifications**

Rotation	<b>Reversible</b>	Mounting	<b>Special</b>
Shaft Type	<b>Parallel</b>	Overall Length	<b>13.81 in</b>
Frame Length	<b>6.75 in</b>	Shaft Diameter	<b>0.750 in</b>
Shaft Extension	<b>1.625 in</b>	Torque	<b>320 LB-IN</b>
Outline Drawing	<b>027696-096013</b>	Connection Drawing	<b>005010.01</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2022

027696




CATALOG NUMBER	OUTPUT RPM	FULL LOAD TORQUE LB.-IN.	INPUT HP	OVERHUNG LOAD LBS.	RATIO TO 1
096013.00	58	320	1/3	300	30
096014.00	85	218	1/3	300	20
096015.00	173	109	1/3	300	10
096016.00	345	55	1/3	300	5

NOTE: WHEN USING MOUNTING BRACKET OHL MUST NOT EXCEED 200 LBS.

		TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN	DWF
		DEC.	INCHES		CHK	DWF
		.X	±.1	TITLE		
		.XX	±.03	OUTLINE - 42 FRAME		
02	THREAD DEPTH WAS .63"	.XXX	±.005	PE350 STOCK	SCALE	5=8
01	ADDED NOTE "DECAL - CONN UNDERCOVER"	.XXXX	±.0005		REF	027689
NO.	REVISION	BY & DATE	CHK	ANG	FINISH	PREV
			RFP	±1/2"	LEESON STOCK	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				CAD FILE	027696	REV.
				DIST	SIZE	DRAWING NO.
					B	027696
						02

005010-01

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



VOLTAGE	L1	L2	L3	JOIN & INSULATE
HIGH	T1	T2	T3	(T4,T7) (T5,T8) (T6,T9)
LOW	T1,T7	T2,T8	T3,T9	T4,T5,T6

				TOLERANCES UNLESS SPECIFIED		<b>Regal Beloit America, Inc.</b>		DRAWN RDW 04/12/02				
				DEC.	INCHES			CHK				
				.X	±.1			APPD				
				.XX	±.01			SCALE 1=1				
				.XXX	±.005	TITLE		REF FIG.2-51				
A	UPDATED TO REGAL LOGO			SAJ	06/26/15	AJY	.XXXX	±.0005	MAT'L. DECAL - 004014	FMF		
NO.	REVISION			BY & DATE	CHK	ANG	±1/2"	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	04/12/02		CAD FILE	00501001		SIZE	DRAWING NO.	REV.
				DIST	BRF-NLV			A	005010-01		A	