

PRODUCT INFORMATION PACKET



Model No: 108423.00

Catalog No: 108423.00

White Duck™ Washdown Motor, 0.25 HP, 90 V, 1750 RPM, S56C Frame, TENV



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications


Output HP	0.25 Hp	Output KW	0.19 kW
Voltage	90 V	Speed	1750 rpm
Service Factor	1.0	Frame	S56C
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Efficiency	68 %	Ambient Temperature	40 °C
Current	2.7 A	Duty	Continuous
Insulation Class	F	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	10.63 in	Frame Length	4.47 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Torque	9 LB-IN		
Outline Drawing	031900-108423	Connection Drawing	00531901

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/08/2025





CONNECTIONS SHOWN FOR CCW ROTATION FACING LEAD END OF THE MOTOR
TO REVERSE ROTATION INTERCHANGE LINE LEADS


				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN TJF 11/15/97		
				DEC.	INCHES		CHK		
F	CHG FROM LEESON TO RRX TEMPLATE AS PER ECR-0237142	KVDG 09/19/24	DS	.X	±.1		APPD POW 11/15/97		
E	"MOTOR" WAS "ARMATURE", ECO-0163602	IPG 3/14/19		.XX	±.01	TITLE	EXTERNAL WIRING DIAGRAM		SCALE 1=2
D	UPDATED TO MAKE IT GENERIC, ECO-0163547	IPG 3/13/19		.XXX	±.005		PMDc MOTOR		REF
01	REDRAWN ON CAD. REVISED NOTES.	SJB 9/20/2005		.XXXX	±.0005	MAT'L.			FMF
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH			PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE 00531901		SIZE	DRAWING NO.	REV.
			DIST		4 of 5		A	005319.01	F

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE

FOR

DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. C4D17VK9Catalog No. 108423.00HP 0.250RPM 1750DC Volts 90.0N.P. FLA 2.70F.F. 1.38Encl TENVType DNS.F. 1.00Max. Amb. 40.0 Deg CInsul. FFrame S56CDuty Cont

Ra 1.8000 Ohms
 La 14.00 mHenrys
 Ja 5.600 LB-IN²
 Ke 46.78 V/KRPM

Kt 3.954 LB-IN/AMP
 Imax 41.3 AMPS Allowed
 FL Torque 9.000 LB-IN
 FL EFF 68.00 %

Winding W- D56232-1Prepared by S. BernhardtDate 05-22-2009