

PRODUCT INFORMATION PACKET



Model No: 108266.00
Catalog No: 108266.00
SCR Motor, 2 HP, 180 V, 2500 RPM, S56CZ Frame, TEFC



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Voltage	180 V	Speed	2500 rpm
Service Factor	1.0	Frame	S56CZ
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Efficiency	88.1 %	Ambient Temperature	40 °C
Current	8.6 A	Duty	Continuous
Insulation Class	F	Drive End Bearing Size	6205
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	17.89 in	Frame Length	10.47 in
Shaft Diameter	0.875 in	Shaft Extension	2.13 in
Torque	50.4 LB-IN		
Outline Drawing	031897-108266	Connection Drawing	00531901

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/08/2025




CONNECTIONS SHOWN FOR CCW ROTATION FACING LEAD END OF THE MOTOR
 TO REVERSE ROTATION INTERCHANGE LINE LEADS

				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN TJF 11/15/97		
				DEC.	INCHES		CHK		
F	CHG FROM LEESON TO RRX TEMPLATE AS PER ECR-0237142	KVDG 09/19/24	DS	.X	±.1	TITLE	EXTERNAL WIRING DIAGRAM		
E	"MOTOR" WAS "ARMATURE", ECO-0163602	IPG 3/14/19		.XX	±.01		PMDC MOTOR		
D	UPDATED TO MAKE IT GENERIC, ECO-0163547	IPG 3/13/19		.XXX	±.005		SCALE 1=2		
01	REDRAWN ON CAD. REVISED NOTES.	SJB 9/20/2005		.XXXX	±.0005	MAT'L.	REF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH	FMF		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP	CAD FILE		00531901	SIZE	DRAWING NO.	REV.
			DIST				A	005319.01	F
						4 of 5			

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE FOR DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. <u>C4D28FK12</u>	Catalog No. <u>108266.00</u>	
HP <u>2.000</u>	RPM <u>2500</u>	DC Volts <u>180.0</u>
F.F. <u>1.38</u>	Encl <u>TEFC</u>	Type <u>DF</u>
Max. Amb. <u>40.0 Deg C</u>	Insul. <u>F</u>	Frame <u>S56CZ</u>
		N.P. FLA <u>8.60</u>
		S.F. <u>1.00</u>
		Duty <u>Cont</u>



Ra 0.6200 Ohms
La 9.500 mHenrys
Ja 22.40 LB-IN²
Ke 70.89 V/KRPM

Kt 5.992 LB-IN/AMP
Imax 103.1 AMPS Allowed
FL Torque 50.40 LB-IN
FL EFF 88.10 %

Winding W- D56233-1 **Prepared by** S. Bernhardt **Date** 05-14-2009