

PRODUCT INFORMATION PACKET



Model No: 108711.00
Catalog No: 108711.00
Parallel Shaft Gearmotor, 0.50 HP, 90 V, 92 RPM, 48Y Frame, TEFC



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications


Output HP	0.50 Hp	Output KW	0.37 kW
Voltage	90 V	Current	5.0 A
Speed	92 rpm	Service Factor	1
Efficiency	66.9 %	Duty	Continuous
Insulation Class	F	Frame	48Y
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications


Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	16.31 in
Frame Length	5.97 in	Shaft Diameter	0.750 in
Shaft Extension	1.5 in	Torque	320 LB-IN
Outline Drawing	032031-108711	Connection Drawing	00531901

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/20/2022

005319.01



CONNECTIONS SHOWN FOR CCW ROTATION FACING LEAD END OF THE MOTOR
TO REVERSE ROTATION INTERCHANGE LINE LEADS


				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN TJF 11/15/97			
				DEC.	INCHES		CHK			
				.X	±.1		APPD POW 11/15/97			
E	"MOTOR" WAS "ARMATURE", ECO-0163602	IPG 3/14/19		.XX	±.01	TITLE EXTERNAL WIRING DIAGRAM PMDC MOTOR		SCALE 1=2		
D	UPDATED TO MAKE IT GENERIC, ECO-0163547	IPG 3/13/19		.XXX	±.005			REF		
01	REDRAWN ON CAD. REVISED NOTES.	SJB 9/20/2005		.XXXX	±.0005	MAT'L.		FMF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH		PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE 00531901		SIZE	DRAWING NO.		REV.
			DIST				A	005319.01		E

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE

FOR

DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. C4D17FZ27Catalog No. 108711.00HP 0.500RPM 92DC Volts 90.0N.P. FLA 5.00F.F. 1.38Encl TEFCType DFS.F. 1.00Max. Amb. 40.0 Deg CInsul. FFrame P1102-48Duty Cont

Ra 1.0300 Ohms
 La 10.04 mHenrys
 Ja 7.188 LB-IN²
 Ke 51.83 V/KRPM

Kt 4.381 LB-IN/AMP
 Imax 66.8 AMPS Allowed
 FL Torque 320.0 LB-IN
 FL EFF 72.70 %

Winding W- D55284-1Prepared by V. BoehlenDate 11-07-2005