

PRODUCT INFORMATION PACKET



Model No: 108369.00
Catalog No: 108369.00
Metric Motor, 180 V, 1800 RPM, 80 Frame, IP54



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output KW	0.75 kW	Voltage	180 V
Speed	1800 rpm	Service Factor	1
Frame	80	Thermal Protection	No Protection
Efficiency	82 %	Ambient Temperature	40 °C
Current	4.9 A	Duty	S1
Insulation Class	F	Drive End Bearing Size	6204
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	Y

Technical Specifications

Rotation	Reversible	Mounting	Special
Overall Length	14.15 in	Frame Length	6.47 in
Shaft Diameter	0.750 in	Shaft Extension	2.05 in
Torque	27 LB-IN		
Connection Drawing	00531901	Outline Drawing	031898-108369

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/09/2025




CONNECTIONS SHOWN FOR CCW ROTATION FACING LEAD END OF THE MOTOR
 TO REVERSE ROTATION INTERCHANGE LINE LEADS

				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN TJF 11/15/97		
				DEC.	INCHES		CHK		
F	CHG FROM LEESON TO RRX TEMPLATE AS PER ECR-0237142	KVDG 09/19/24	DS	.X	±.1	TITLE	EXTERNAL WIRING DIAGRAM		
E	"MOTOR" WAS "ARMATURE", ECO-0163602	IPG 3/14/19		.XX	±.01		PMDC MOTOR		
D	UPDATED TO MAKE IT GENERIC, ECO-0163547	IPG 3/13/19		.XXX	±.005		SCALE 1=2		
01	REDRAWN ON CAD. REVISED NOTES.	SJB 9/20/2005		.XXXX	±.0005	MAT'L.	REF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH	FMF		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP	CAD FILE		00531901	SIZE	DRAWING NO.	REV.
			DIST				A	005319.01	F
						4 of 5			

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE FOR DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. CI4D17FT1 **Catalog No.** 108369.00
KW 0.550 **RPM** 1800 **DC Volts** 180.0 **N.P. FLA** 3.80
F.F. 1.38 **Encl** IP54 **Type** 80-14 **S.F.** 1.00
Max. Amb. 40.0 Deg C **Insul.** F **Frame** 80D **Duty** S1



Ra <u>2.6500</u> Ohms La <u>27.40</u> mHenrys Ja <u>30.43</u> KG-CM^2 Ke <u>94.44</u> V/KRPM	Kt <u>0.9019</u> N-M/AMP Imax <u>39.3</u> AMPS Allowed FL Torque <u>2.972</u> N-M FL EFF <u>82.00</u> %
---	--

Winding W- D56224-1 **Prepared by** S. Bernhardt **Date** 05-06-2009