

# PRODUCT INFORMATION PACKET



Model No: 113924.00  
Catalog No: 113924.00  
Special Voltage Motor, 1 HP, 1 Ph, 50 Hz, 110/220 V, 1500 RPM, 56C Frame, TEFC



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E







**Nameplate Specifications**

Phase	1	Output HP	1 Hp
Output KW	0.75 kW	Voltage	110/220 V
Speed	1425 rpm	Service Factor	1
Frame	56C	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Manual	Efficiency	73 %
Ambient Temperature	40 °C	Frequency	50 Hz
Current	12.8/6.4 A	Power Factor	71
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	J
Drive End Bearing Size	6203	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	54
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	2.12 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	NEMA 56	Overall Length	12.48 in
Frame Length	7.00 in	Shaft Diameter	0.625 in
Shaft Extension	1.88 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005382.02	Outline Drawing	029087-700B



NOTE:-  
1) GASKET THROUGHOUT.



DRAWING REVISION A	REVISION BY	DATE
ECO ECO-0140840	APPROVED BY	DATE
ECO DESCRIPTION <b>OUTLINE CONVERSION PROJECT</b> COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

TOLERANCES UNLESS OTHERWISE SPECIFIED:			
DEC.	INCH	mm	ANGLE
.X	±0.1	[±2.5]	±7° 30"
.XX	±0.03	[±0.76]	
.XXX	±0.005	[±0.127]	
.XXXX	±0.0005	[±0.0127]	
REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [0.51] MACHINED SURFACES: 200 INCH/mm 5.1 mm SHOWN IN [BRACKETS]			

DASH No.	"C"	"AD"	CAP DASH.	"XO"
700	12.49 [317.25]	6.69 [169.93]	B	2.01 [51.05]
DRAWN BY A SUPPANAVAR	Regal Beloit America, Inc.			
DATE 01/15/2018				
APPROVED BY PK	DESCRIPTION <b>OUTLINE</b> 56C FRAME TEFC- "C" FACE			
DATE 03/08/2018	MATERIAL			
REFERENCE 028980	PROCESS/FINISH			
THIRD ANGLE PROJECTION	SIZE B	DRAWING NUMBER 029087	SHEET 1 OF 1	

REV	REFERENCE ECN	REFERENCE PROJECT	REV BY	DATE	APPD	DATE
J.00	ECN-01172301	PRJ-01172301	sbowli	10-13-2005		

60P84



**NOTES:**

1. U.L. RECOGNIZED CAPACITOR. UL MARKING TO BE STAMPED ON CAPACITORS.
2. METALLIZED POLYPROPYLENE CAPACITOR.
3. MAX. OPERATING TEM. -85° C.
4. POTTING COMPOUND CAN BE EITHER BLACK (URETHANE) OR BLUE (POLYURETHANE).

22	3	250	.58	1.02	1.44	1	JE2E032	2
21	3	370	.75	1.15	1.46	1	JF1G095	G
20	OBSOLETE							
19	6	250	.58	1.02	1.44	2	JF1G072	2
18	2.5	250	.58	1.02	1.44	1	JE2C005	2
17	5	250	.58	1.02	1.44	2	JF1G072	2
16	2	370	.75	1.15	1.46	1	JE2F032	G
15	2	250	.58	1.02	1.44	1	JE2E020	2
14	OBSOLETE							
13	6	250	.58	1.02	1.44	1	JE2F025	2
12	10	250	.75	1.15	1.46	1	CE2F014	G
11	5	250	.58	1.02	1.44	1	JE1E017	2
10	4	250	.58	1.02	1.44	1	JE1D006	2
9	7.5	250	.75	1.15	1.46	1	JE1E015	G
8	4	370	.88	1.26	2.11	1	JE1D006	6
7	5	370	.88	1.26	2.11	1	JE1E017	6
6	6	370	.88	1.26	2.11	1	JE1E016	6
5	7.5	370	.93	1.40	2.30	1	JE1E015	E
4	5	370	.88	1.26	2.11	2	JE1H030	6
3	OBSOLETE							
2	4	250	.58	1.02	1.44	1	JE1E011	2
1	15	250	.88	1.26	2.11	1	JE2G071	6
GR. NO.	MFD ±10%	VAC	T	H	W	VIEW	FIRST USED ON	CASE SIZE

USE GRP. 10

**GEOMETRIC CHARACTERISTICS & SYMBOLS**  
 □ FLATNESS  
 — STRAIGHTNESS  
 ∠ ANGULARITY  
 ⊥ PERPENDICULARITY (SQUARENESS)  
 // PARALLELISM  
 ○ ROUNDNESS (CIRCULARITY)  
 Ⓞ CYLINDRICITY  
 △ PROFILE OF ANY SURFACE  
 ⌒ PROFILE OF ANY LINE  
 ↗ RUNOUT  
 ⊕ TRUE POSITION  
 ⊙ CONCENTRICITY  
 = SYMMETRY

UNLESS OTHERWISE SPECIFIED DIM. TOLERANCES ARE AS FOLLOWS:  
 X XX XXX XXXX  
 INCH ±.1 ±.02 ±.005 ±.0005  
 mm ±0.5 ±0.13 ±0.013  
 ANG. ±.50 DEG  
 REMOVE BURRS & BREAK SHARP EDGES:  
 INCH .003-.015 mm 0.1-0.4  
 CORNER FILLETS TO:  
 INCH .020 mm 0.5  
 MACHINE SURFACES:  
 INCH 125 mm 3:2  
 METRIC DIMS. SHOWN IN [BRACKETS]

DR BY: jimerm  
 12-03-2002  
 APPD:  
 THIRD ANGLE PROJECTION  
 CONFIDENTIAL: THIS DRAWING AND ITS INFORMATION ARE THE EXCLUSIVE AND CONFIDENTIAL PROPERTY OF A.O. SMITH CORP. AND ARE NOT TO BE DISCLOSED, DUPLICATED, DISTRIBUTED OR OTHERWISE USED WITHOUT THE WRITTEN CONSENT OF A.O. SMITH CORP.  
 -ALL RIGHTS RESERVED.

EDS DATE  
 FORMAT REV B

**A.O. SMITH**  
 ELECTRICAL PRODUCTS COMPANY  
TIPP CITY, OHIO

A DIVISION OF A. O. SMITH CORPORATION  
COPYRIGHT 1995

DESCRIPTION  
**DRY FILM CAPACITOR**  
**60P84**

SCALE NONE

DWG NO 00538202

SHEET 1



1051 CHEYENNE AVE.  
GRAFTON, WI 53024  
PH. 262-377-8810

CONN. DIAGRAM: 005382.02  
OUTLINE: 029087-700B  
WINDING #: C634266 FR 4 C

CATALOG #: 113924.00

MOUNTING: F1 ONLY

**TYPICAL MOTOR PERFORMANCE DATA**

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
1	0.75	1500	1425	56C	TEFC	J	NO DESIGN CODE

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	50	110/220	12.8/6.4	ACROSS THE LINE	CONTINUOUS	F4	1.0	40

FULL LOAD EFF:	73	3/4 LOAD EFF:	67.5	1/2 LOAD EFF:	63.2	GTD. EFF	ELEC. TYPE
FULL LOAD PF:	71	3/4 LOAD PF:	63.2	1/2 LOAD PF:	52	68	CAP START IND RUN

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
3.6 LB-FT	57.2 / 28.6	9 LB-FT 250 %	8.17 LB-FT 227 %	64.1

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
0 dBA	10 dBA	0.12 LB-FT^2	0 LB-FT^2	10 SEC.	0	37 LBS.

**\*\*\* SUPPLEMENTAL INFORMATION \*\*\***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	ROUND	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE - LEESON (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	STANDARD 56	NONE	NONE	1144 STRESSPROOF (C-223)	ROLLED STEEL
6203	6203						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	MANUAL	NONE	NONE	NONE	FALSE	NONE VOLTS

<b>INVERTER TORQUE:</b> NONE <b>INV. HP SPEED RANGE:</b> NONE
<b>ENCODER:</b> NONE NONE NONE NONE NONE PPR
<b>BRAKE:</b> NONE NONE NONE P/N NONE NONE NONE NONE FT-LB NONE V NONE Hz

\*  
N  
O  
T  
E  
S  
\*



## EC Declaration of Conformity

The undersigned representing  
the manufacturer:

Regal Beloit America  
1946 West Cook Road  
Fort Wayne, IN 46818

and the authorized representative  
established within the Community:

Regal Beloit Italy  
Via Modena, 18  
24040 Ciserano(BG) - Italy

are committed to providing customers with products that comply with applicable regulations and international protocols to which they are subject, including the requirements of the European Parliament Directive on the Harmonization of the laws relating to electrical equipment designed for use within certain voltage limits (2014/35/EU).

Regal Beloit America declares that the following product(s), to which this declaration relates, are in conformity with the relevant sections of the EC standards listed below.

This statement supersedes any statements previously issued pertaining to the product(s) listed below and is subject to change without notice.

Model No : 113924.00

(Model No. may contain prefix and/or suffix characters)

Catalog No : 113924.00

Rework No : N/A

Directives :

Low Voltage Directive 2014/35/EU

Harmonized Standards Used :

EN 60034-1: 2010 (IEC 60034-1: 2010)

EN 60034-5: 2001/A1:2007 (IEC 60034-5: 2000/A1:2006)

Authorized Representative:



Zach Stauffer  
Vice President, Engineering

Authorized Representative in the Community:



Stefano Casiraghi  
Technology Director, Engineering

Created on 07/08/2025

**CE 25**