

PRODUCT INFORMATION PACKET



Model No: 116351.00

Catalog No: 116351.00

Premium Duck™ General Purpose Motor, 0.75 HP, 1 Ph, 60 Hz, 115/230 V, 1800 RPM, 56C Frame, TENV

Operational at 115/208-230 V @60HZ



Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	1	Output HP	0.75 Hp
Output KW	0.56 kW	Voltage	115/230 V
Speed	1725 rpm	Service Factor	1.15
Frame	56C	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Efficiency	77 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	7.6/3.8 A	Power Factor	84
Duty	Continuous	Insulation Class	F
Design Code	N	KVA Code	K
Drive End Bearing Size	6205	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	N	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	NEMA 56	Overall Length	12.70 in
Frame Length	8.00 in	Shaft Diameter	0.625 in
Shaft Extension	1.88 in	Assembly/Box Mounting	F1 ONLY
Outline Drawing	034992-800	Connection Drawing	005259.03



SPECIAL FEATURES:

- VITON CONDUIT BOX & COVER GASKETS
- VITON O-RINGS IN ENDBELL RABBETS
- VITON SHAFT SEAL
- BREATHER PLUGS IN L.E. ENDBELL (B.I.C.B.)
- ALL STAINLESS STEEL CONSTRUCTION

DASH NO.	"C"	"AD"
700	11.70	8.25
750	12.20	8.75
800	12.70	9.25
850	13.20	9.75
900	13.70	10.25

MAXIMUM FACE RUNOUT TO BE .004 T.I.R.
 MAXIMUM PILOT ECCENTRICITY .004 T.I.R.
 PERMISSIBLE SHAFT RUNOUT .002 T.I.R.


				TOLERANCES UNLESS SPECIFIED		LEESON	ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN	LST 3/25/03
				DEC.	INCHES			CHK	RW 3/25/03
				.X	±.1			APPD	
				.XX	±.03	TITLE	OUTLINE- 56C FRAME TENV- "C" FACE	SCALE	3=8
02	ADDED HOLE PLUGS PER ECO 03-617	LST 8/7/03	.XXX	±.005	MAT'L.	STAINLESS STEEL DUCK	REF	034991	
01	REVISED NAMEPLATE	JJK 7/24/03	.XXXX	±.0005	FINISH		FMF	116349	
NO.	REVISION	BY & DATE	CHK	ANG ±1/2°	PREV				
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE	034992	SIZE	DRAWING NO.	REV.
				DIST			A	034992	02

```
ERROR: syntaxerror  
OFFENDING COMMAND: --nostringval--
```


```
STACK:
```

```
/initialize  
-dictionary-  
/Pscript_WinNT_Compat  
-dictionary-
```

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



*THIS LEAD MAY BE WHITE



				TOLERANCES UNLESS OTHERWISE SPECIFIED		LEESON ELECTRIC CORPORATION					
				DECIMALS							
				.00	± .01	DRAWN KMM 12/16/94		TITLE		EXTERNAL WIRING DIAGRAM TYPE "K" W/O PROTECTOR	
				.000	± .005	CH'K'D.					
02	REDRAWN, UPDATED TO CURRENT STANDARDS		DBT	12/18/97	.0000	± .0005	APPR.		MAT'L. W/SOLID STATE SWITCH DECAL - 004012		
NO.	REVISION		BY	DATE	FRACTIONS	± 1/64	SCALE 1=1				
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED					ANGLES	± 1/2°	REF. 005259-02	FINISH DTS		SIZE	DRAWING NO.
					INCH/MM		FMF 114559	FLUID		A	005259-03



1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810

CERTIFICATION DATA SHEET

CONN. DIAGRAM: 005259.03
OUTLINE: 034992-800
WINDING #: K634294 NR 3 A

CATALOG #: 116351.00
MOUNTING: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
3/4	0.56	1800	1725	56C	TENV	K	N

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	115/208-230	7.6/4.2-3.8	ACROSS THE LINE	CONTINUOUS	F4	1.15	40

FULL LOAD EFF:	77	3/4 LOAD EFF:	70.5	1/2 LOAD EFF:	63.3	GTD. EFF	ELEC. TYPE
FULL LOAD PF:	84	3/4 LOAD PF:	81.6	1/2 LOAD PF:	75.2	74	CAP START CAP RUN

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
36 OZ-FT	56 / 28	128 OZ-FT 474 %	97.3 OZ-FT 360 %	90

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
60 dBA	70 dBA	0.11 LB-FT^2	0 LB-FT^2	0 SEC.	0	42 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
C-FACE	STANDARD	ROUND	HORIZONTAL	FALSE	NONE	FALSE	NONE	NO PAINT

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	STANDARD 56	NONE	NONE	303 STAINLESS (C-501)	ROLLED STEEL
6205	6203						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

*
N
O
T
E
S
*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE
ENCODER: NONE NONE NONE NONE NONE PPR
BRAKE: NONE NONE NONE P/N NONE NONE NONE NONE FT-LB NONE V NONE Hz




LEESON ELECTRIC CORPORATION
TYPICAL PERFORMANCE CURVE for AC MOTOR

Model No 116351.00

Catalog No 116351.00

Curve at 230 Volts HP 0.76 PHASE 1
60 HZ
0.75 HP VOLTS 115/208-230

HZ 60 RPM 1725



FL TORQUE	<u>36</u>	Oz.Ft	FL AMPS	<u>7.6/4.2-3.8</u>
BD TORQUE	<u>97.3</u>	Oz.Ft	PU TORQUE	<u>89.0</u> Oz.Ft
LR TORQUE	<u>128</u>	Oz.Ft	LR AMPS	<u>28</u>
WINDING	K634294-3		Date	<u>3/26/2018</u>