

PRODUCT INFORMATION PACKET



Model No: 116642.00

Catalog No: 116642.00

White Duck™ General Purpose Motor, 0.33 & 0.25 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V,
1800 & 1500 RPM, 56C Frame, TEFC

Operational at 208-230/460 V @60HZ



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E







Nameplate Specifications

Phase	3	Output HP	0.33 & 0.25 Hp
Output KW	0.25 & 0.19 kW	Voltage	230/460 & 190/380 V
Speed	1725 & 1425 rpm	Service Factor	1.15 & 1.15
Frame	56C	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	68 & 62 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	1.7/.85 & 1.6/.8 A	Power Factor	54
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	L
Drive End Bearing Size	6205	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	NEMA 56	Overall Length	10.37 in
Frame Length	4.50 in	Shaft Diameter	0.625 in
Shaft Extension	1.88 in	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005010.01	Outline Drawing	607-0006-450




DASH NO.	"C"	"AD"
450	10.37	4.56
500	10.87	5.06
550	11.37	5.56
600	11.87	6.06
650	12.37	6.56
675	12.62	6.81
700	12.87	7.06
750	13.37	7.56
775	13.62	7.81
800	13.87	8.06


WASHGUARD MOTOR
 SPECIAL FEATURES:
 1. SHAFT SEALS & V-RING.
 2. PLUGGED DRAIN HOLES IN ENDBELLS & CONDUIT BOX.
 3. BUNA-N GASKETS THROUGHOUT.
 4. STAINLESS STEEL SHAFT, HARDWARE & NAMEPLATE.

DRAWING REVISION D	REVISION BY SAJID	DATE 10/01/2015	TOLERANCES UNLESS OTHERWISE SPECIFIED: <table border="1"> <tr> <th>DEC.</th> <th>INCH</th> <th>mm</th> <th>ANGLE</th> </tr> <tr> <td>.X</td> <td>± 0.1</td> <td>[± 2.5]</td> <td>$\pm 0.5^\circ$</td> </tr> <tr> <td>.XX</td> <td>± 0.01</td> <td>[± 0.25]</td> <td></td> </tr> <tr> <td>.XXX</td> <td>± 0.005</td> <td>[± 0.127]</td> <td></td> </tr> <tr> <td>.XXXX</td> <td>± 0.0005</td> <td>[± 0.0127]</td> <td></td> </tr> </table> REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 125 $\sqrt{\text{INCH}}$ 3.2 $\sqrt{\text{mm}}$ mm SHOWN IN [BRACKETS]	DEC.	INCH	mm	ANGLE	.X	± 0.1	[± 2.5]	$\pm 0.5^\circ$.XX	± 0.01	[± 0.25]		.XXX	± 0.005	[± 0.127]		.XXXX	± 0.0005	[± 0.0127]		DRAWN BY PG 02/08/11	Regal Beloit America, Inc.
DEC.	INCH	mm		ANGLE																					
.X	± 0.1	[± 2.5]	$\pm 0.5^\circ$																						
.XX	± 0.01	[± 0.25]																							
.XXX	± 0.005	[± 0.127]																							
.XXXX	± 0.0005	[± 0.0127]																							
ECO ECO-0081887	APPROVED BY	DATE	DATE	DESCRIPTION OUTLINE TEFC - "C" FACE																					
ECO DESCRIPTION ADDED ITEMS #800			COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.	APPROVED BY	MATERIAL WASHGUARD	PROCESS/FINISH																			
				DATE	REFERENCE	SIZE B	DRAWING NUMBER 607-0006																		
				THIRD ANGLE PROJECTION		SHEET 1 OF 1																			

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



LINE LEADS



VOLTAGE	L1	L2	L3	JOIN & INSULATE
HIGH	T1	T2	T3	(T4, T7) (T5, T8) (T6, T9)
LOW	T1, T7	T2, T8	T3, T9	T4, T5, T6

RBC PROPRIETARY AND CONFIDENTIAL INFORMATION
 This document is the property of REGAL BELOIT CORPORATION ("RBC") including its subsidiaries and divisions and contains proprietary information of RBC. This document is loaned on the express condition that neither it nor the information contained therein shall be disclosed to others without the express written consent of RBC, and that the information shall be used by the recipient only as approved expressly by RBC. This document shall be returned to RBC upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.

				TOLERANCES UNLESS SPECIFIED		DRAWN RDW 04/12/02	
				DEC	INCHES	CHK	
				.X	±.1	APPR	
12	CHG FROM LEESON TO RRX TEMPLATE AS PER ECR-0237142	KVDG 09/19/24	DS	.XX	±.01	TITLE EXTERNAL WIRING DIAGRAM	
--	REDRAWN IN SOLIDWORKS	VJB 02/08/11		.XXX	±.005	3 PHASE W/O PROTECTOR	
11	ADD REV TO MATCH ORACLE	KJH 06/08/09	MDN	.XXX	±.0005	MAT'L DECAL - 004014	
NO	REVISION	BY & DATE	CHK	ANG	±1/2°	FINISH	
			RFP	04/12/02	PREV	SIZE	DRAWING NO
THIRD ANGLE PROJECTION			NETWORK FILE NAME		00501001	A	005010-01
							REV
							12




LEESON ELECTRIC CORPORATION
 TYPICAL PERFORMANCE CURVE for AC MOTOR

Model No 116642.00

Catalog No 116642.00

Curve at 460 Volts HP 0.34&0.26 PHASE 3
60 HZ
0.33 HP VOLTS 208-230/460&190/380

HZ 60&50 RPM 1725&1425



Torque in Oz.Ft

FL TORQUE 16 Oz.Ft
 BD TORQUE 80.0 Oz.Ft
 LR TORQUE 46.7 Oz.Ft

FL AMPS 1.6-1.7/.85
 PU TORQUE 60.0 Oz.Ft
 LR AMPS 3.65

WINDING T634201-3

Date 5/22/2018

EC Declaration of Conformity

The undersigned representing
the manufacturer:

Regal Beloit America
1946 West Cook Road
Fort Wayne, IN 46818

and the authorized representative
established within the Community:

Regal Beloit Italy
Via Modena, 18
24040 Ciserano(BG) - Italy

are committed to providing customers with products that comply with applicable regulations and international protocols to which they are subject, including the requirements of the European Parliament Directive on the Harmonization of the laws relating to electrical equipment designed for use within certain voltage limits (2014/35/EU).

Regal Beloit America declares that the following product(s), to which this declaration relates, are in conformity with the relevant sections of the EC standards listed below.

This statement supersedes any statements previously issued pertaining to the product(s) listed below and is subject to change without notice.

Model No : 116642.00

(Model No. may contain prefix and/or suffix characters)

Catalog No : 116642.00

Rework No : N/A

Directives :

Low Voltage Directive 2014/35/EU

Harmonized Standards Used :

EN 60034-1: 2010 (IEC 60034-1: 2010)

EN 60034-5: 2001/A1:2007 (IEC 60034-5: 2000/A1:2006)

Authorized Representative:



Zach Stauffer
Vice President, Engineering

Authorized Representative in the Community:



Stefano Casiraghi
Technology Director, Engineering

Created on 07/08/2025

CE 25