


PRODUCT INFORMATION PACKET



Model No: C215K34NB73A

Catalog No: 141220.00

..10-15 -HP..3600RPM.215TZ.TEAO.230V.1PH.60HZ.CONT.50C.1.0SF.RIGID.....CROP DRYER.....
Crop Dryer



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230 V
Current	45.8 A	Speed	3475 rpm
Service Factor	1.5	Phase	1
Efficiency	82.5 %	Duty	Continuous
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	D	Frame	215TZ
Enclosure	Totally Enclosed Air Over	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6307
Opp Drive End Bearing Size	6206	UL	Recognized
CSA	Y	CE	N
IP Code	43		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Mounting	Rigid base	Motor Orientation	HORIZONTAL
Drive End Bearing	BALL	Opp Drive End Bearing	BALL
Frame Material	Rolled Steel	Shaft Type	Single Special Extension
Overall Length	18.17 in	Frame Length	11.15 in
Shaft Diameter	1.125 in	Shaft Extension	3.75 in
Assembly/Box Mounting	F3		
Outline Drawing	038026-1115	Connection Diagram	EE7090KL

038026



NOTES:

1. NAMEPLATE TO BE READ FROM "A" SIDE OF MOTOR.
2. SEE MODEL FOR LEAD LENGTH.


DASH	FR.	C	BS	
965	213T	16.67	5.43	
1115	213/15T	18.17	6.93	
1240	213/15T	19.42	8.18	F1 ONLY

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN SAJ 7/7/15	
				DEC.	INCHES		CHK SR 7/7/15	
				.X	$\pm .1$		APPD	
				.XX	$\pm .03$		SCALE 1=4	
				.XXX	$\pm .005$	TITLE OUTLINE 210TZ FR. - BB - SS - TENV - 1 ϕ	REF OLSPR112641	
				.XXXX	$\pm .0005$		FMF	
				ANG	$\pm 7'30''$	FINISH	PREV	
01	NEW DRAWING	SAJ 7/7/15	SR	.XXXX	$\pm .0005$	MAT'L.		
NO.	REVISION	BY & DATE	CHK	ANG	$\pm 7'30''$	FINISH	SIZE	DRAWING NO. PAGE OF REV.
							A	038026 01


THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT

RFP
DIST LB

CAD FILE 038026

SINGLE VOLTAGE CAPACITOR START
MOTOR, ELECTRICALLY REVERSIBLE

P1 & P2 ARE
THERMAL PROTECTOR
LEADS



VIEW OF TERMINAL END

				✓ MAX. SURFACE ROUGHNESS UNLESS NOTED OTHERWISE	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOL. ON XX±.02 XXX±.005 XXXX±.0005 ANGLES± 7°30"					
2	11-3-95	REVISED - P2 LEAD WAS P1 CN 20775-671	KL	MATL SPEC	180-210 SWITCH		DRAWN BY	BLR	8-24-95	
				FINISH			CHKD BY	DA	8-24-95	
1	08-24-95	NEW DRAWING 4311347	BLR	PART NAME CONNECTION DIAGRAM				APPD BY	PH	8-24-95
REV	DATE	CHANGE	NAME					DRWG NO A- EE709OKL		
SHOP BOOK		PURCHASED	DISTRIBUTION - WA - LB - WP - LM			CADD FILE NO.		EE709OKL		

ERROR: syntaxerror
OFFENDING COMMAND: --nostringval--

STACK:

-dictionary-
-dictionary-
/Pscript_winNT_Compat
-dictionary-