

PRODUCT INFORMATION PACKET

Model No: M1125050.00

Catalog No: M1125050.00

Parallel Shaft Gearmotor, 0.01 HP, 1 Ph, 60 Hz, 115 V, 2 RPM, 31 Frame, TENV



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E


Nameplate Specifications

Output HP	0.01 Hp	Output KW	0.03 kW
Frequency	60 Hz	Voltage	115 V
Current	0.40 A	Speed	2 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
KVA Code	L	Frame	31
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	6000
Opp Drive End Bearing Size	R6	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	8.71 in
Frame Length	3.87 in	Shaft Diameter	0.500 in
Shaft Extension	1 in	Torque	100 LB-IN
Outline Drawing	M1030348-M1125080	Connection Drawing	M1005089.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2022




CAT. NO.	HP	RATIO NOMINAL	SAFE TORQUE LB.-IN	RPM OUT-PUT	"XL" DIM.	"X" DIM.	"XH" DIM.
M1125050.00	1/150	900:1	100	1.9	8.71	3.23	7.15
M1125051.00	1/15	180:1	100	9.4	9.46	3.23	7.90
M1125052.00	1/15	90:1	100	19	9.46	3.23	7.90
M1125053.00	1/15	60:1	100	28	8.90	2.48	7.34
M1125054.00	1/15	30:1	56	57	8.90	2.48	7.34
M1125055.00	1/15	18:1	36	94	8.90	2.48	7.34
M1125056.00	1/15	12:1	24	142	8.61	2.14	7.05
M1125057.00	1/15	6:1	12	283	8.61	2.14	7.05

NOTES:

- 1- ALL GEARING IS STEEL IN COMPOSITION.
- 2- GEARING IS OF AGMA #8 QUALITY OR BETTER.

06	ROTATED SHAFT FLAT 180°, PER ECR 79989	RLW 7/24/02		TOLERANCES UNLESS SPECIFIED	LEESON	ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN DWF 08/27/93		
05	M1125050, M1125051 & M1125052 "X" DIM WAS 2.98	BPW 12/03/01	DEC.	INCHES			CHK		
04	M1125050.00 "XL" DIM WAS 8.46	TMZ 06/22/95	.X	±.1			APPD SPV 09/03/93		
	"XH" DIM WAS 6.90		.XX	±.03			SCALE 3=4		
03	ADDED TORQUE'S AND RPM	SPV 05/16/95	DWF	.XXX	±.005	TITLE OUTLINE DRAWING 31 FRAME A.C.	REF PR930265		
02	ADDED NEW CON BOX, OPTIONAL BASE	SPV 04/25/95		.XXXX	±.0005	MAT'L	FMF M1125051.00		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH	PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT					RFP	CAD FILE M1030348	SIZE B	DRAWING NO. M1030348	REV. 06
					DIST				



CONNECTIONS SHOWN FOR CCW ROTATION FACING LEAD END.
TO REVERSE ROTATION INTERCHANGE T4(YELLOW) AND T1(BLUE) LEADS

				TOLERANCES UNLESS OTHERWISE SPECIFIED		LEESON ELECTRIC CORPORATION			
				DECIMALS					
				.00	± .01	DRAWN SJB 12/21/89	TITLE		
02	ADDED T1 AND T4 TO REVERSE INSTUCTIONS	DWD	4/7/97	.000	± .005	CH'K'D.	EXTERNAL WIRING DIAGRAM		
01	REDRAWN ON CAD	RJB PTZ	11/16/92	.0000	± .0005	APPR.	MAT'L. "P" TYPE W/O PROTECTOR		
NO.	REVISION	BY	DATE	FRACTIONS	± 1/64	SCALE 1=1	DUAL ROT., ROT. BASED ON ODD # GEAR STAGE		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED				ANGLES	± 1/2°	REF.	FINISH	SIZE	DRAWING NO.
				INCH/MM		FMF		A	M1005089.01