

PRODUCT INFORMATION PACKET



Model No: M1125006.00
Catalog No: M1125006.00
Parallel Shaft Gearmotor, 0.06 HP, 90 V, 300 RPM, 30 Frame, TENV



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E









Nameplate Specifications

Output HP	0.06 Hp	Output KW	0.04 kW
Voltage	90 V	Speed	300 rpm
Service Factor	1.0	Frame	30
Enclosure	Totally Enclosed Non Ventilating	Thermal Protection	No Protection
Efficiency	57.6 %	Ambient Temperature	40 °C
Current	0.80 A	Duty	Continuous
Insulation Class	F	Drive End Bearing Size	6000
Opp Drive End Bearing Size	6000	UL	Recognized
CSA	Y	CE	Y

Technical Specifications

Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	8.46 in
Frame Length	2.99 in	Shaft Diameter	0.500 in
Shaft Extension	1 in	Torque	10 LB-IN
Connection Drawing	M100530201	Outline Drawing	M1030957-M1125006

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/08/2025



SHAFT DETAIL
SCALE 2:1

CATALOG No.	VOLTS	HP	RATIO	TORQUE IN-LB	RPM	"XL" INCH	"XH" INCH	"X" INCH
M1115000.00	90	1/20	90:1	100	20	9.30	7.74	3.24
M1115001.00	90	1/20	180:1	100	10	9.30	7.74	3.24
M1115002.00	90	1/40	450:1	40	4	9.30	7.74	3.24
M1125002.00	90	1/17	60:1	100	30	8.74	7.18	2.68
M1125003.00	90	1/17	30:1	56	60	8.74	7.18	2.68
M1125004.00	90	1/17	18:1	36	100	8.74	7.18	2.68
M1125005.00	90	1/17	12:1	24	150	8.46	6.90	2.40
M1125006.00	90	1/17	6:1	10	300	8.46	6.90	2.40
M1125033.00	180	1/17	6:1	10	300	8.46	6.90	2.40
M1125034.00	180	1/17	12:1	24	150	8.46	6.90	2.40
M1125035.00	180	1/17	18:1	36	100	8.74	7.18	2.68
M1125036.00	180	1/17	30:1	56	60	8.74	7.18	2.68
M1125037.00	180	1/17	60:1	100	30	8.74	7.18	2.68
M1125046.00	180	1/40	450:1	40	4	9.30	7.74	3.24
M1125047.00	180	1/20	180:1	100	10	9.30	7.74	3.24
M1125048.00	180	1/20	90:1	100	20	9.30	7.74	3.24


				TOLERANCES UNLESS SPECIFIED		ELECTRIC MOTORS GEARMOTORS AND DRIVES		DRAWN RWS 3/7/05	
				DEC. INCHES				CHK RPB 3/8/05	
				.X ±.1				APPD	
				.XX ±.03				SCALE 1=2	
				.XXX ±.005		TITLE		REF M1115000-1125048	
00 RELEASED COMM CONVERSION PROJECT				RWS 4/13/05		MAT'L		FMF M1115002.00	
NO. REVISION				BY & DATE		FINISH		PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE M1030957		SIZE B DRAWING NO. M1030957.00	
				DIST				REV. 00	

ERROR: syntaxerror
OFFENDING COMMAND: --nostringval--

STACK:

/im
-savelevel-

D.C. MOTORS



EXTERNAL CONNECTIONS FOR CW ROTATION
VIEWING LEAD END OF MOTOR WITH RED LEAD
POSITIVE (+) AND BLACK LEAD NEGATIVE (-)
FOR CCW ROTATION REVERSE POLARITY


ITEM	REV
	001

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN RWS 3/15/05	
				DEC.	INCHES		CHK RPB 3/15/05	
				.X	±.1		APPD	
				.XX	±.01		SCALE 1=1	
				.XXX	±.005		REF 901.706	
C	BRUSH HOLDERS ROTATED 90°, ECR-0207997	IPG 11/12/21		.XXX	±.005	TITLE CONNECTION DIAGRAM		SCALE 1=1
00	RELEASED COMM CONVERSION PROJECT	RWS 4/13/05	RPB	.XXXX	±.0005	MAT'L.		REF 901.706
NO.	REVISION	BY & DATE	CHK	ANG	±1/2°	FINISH		FMF M115002.00
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	M100530201	SIZE A
				DIST				DRAWING NO. M1005302.01
								REV. C
								5 of 6

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE FOR DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. <u>985.630</u>	Catalog No. <u>M1125006.00</u>	
HP <u>0.059</u>	RPM <u>300</u>	DC Volts <u>90.0</u>
F.F. <u>1.38</u>	Encl <u>TENV</u>	Type <u>DN</u>
Max. Amb. <u>40.0 Deg C</u>	Insul. <u>F</u>	Frame <u>30</u>
		N.P. FLA <u>0.80</u>
		S.F. <u>1.00</u>
		Duty <u>CONT</u>



Ra 14.400 Ohms
La 55.99 mHenrys
Ja 3.864 OZ-IN²
Ke 39.31 V/KRPM

Kt 3.322 LB-IN/AMP
Imax 8.2 AMPS Allowed
FL Torque 10.00 LB-IN
FL EFF 57.60 %

Winding W- MD302118-2 Prepared by _____ Date 03-02-2020