

PRODUCT INFORMATION PACKET



Model No: M1125269.00
Catalog No: M1125269.00
White Duck™ Parallel Shaft Gearmotor, 0.25 HP, 90 V, 42 RPM, 32 Frame



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	0.25 Hp	Output KW	0.19 kW
Voltage	90 V	Speed	42 rpm
Service Factor	1	Frame	32
Thermal Protection	No Protection	Efficiency	65.3 %
Ambient Temperature	40 °C	Current	2.6 A
Duty	Continuous	Insulation Class	F
Drive End Bearing Size	6201	Opp Drive End Bearing Size	6201
UL	Recognized	CSA	Y
CE	Y		

Technical Specifications

Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	13.84 in
Frame Length	6.44 in	Shaft Diameter	0.750 in
Shaft Extension	1.63 in	Torque	280 LB-IN
Connection Drawing	M100530801	Outline Drawing	M1030991-M1125269

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:05/09/2025




NOTES:
 1) GASKETS BETWEEN FRAME AND ENDBELL/GEARBOX, CONDUIT BOX AND FRAME, AND CONDUIT BOX COVER AND CONDUIT BOX.

CATALOG NUMBER	OUTPUT RPM	FULL LOAD TORQUE LB.-IN.	INPUT HP	OVERHUNG LOAD LBS.	RATIO TO 1
M1125269.00	42	280	1/4	327	58
M1125270.00	83	155	1/4	267	29
M1125271.00	250	45	1/4	201	10
M1125272.00	500	25	1/4	194	5

				TOLERANCES UNLESS SPECIFIED		LEESON ELECTRIC MOTORS GEARMOTORS AND DRIVES		DRAWN IPG 5/14/05		
				DEC.	INCHES			CHK	SAD 5/14/05	
				.X	±.1			APPD		
				.XX	±.03	TITLE		SCALE	1=2	
01	1/2 NPT CONDUIT PLUG QTY. WAS 3. ISAAC 08-3457	RBP	7/30/08	BC	.XXX	±.005	OUTLINE - 32 FRAME DC 90V - PE350 GEARMOTOR		REF	PR040127-RD1
00	RELEASED: REF. PR040127-RD1	IPG	5/14/05	SAD	.XXXX	±.0005	MAT'L		FMF	M1125269.00
NO.		REVISION		BY & DATE		FINISH <th colspan="2">PREV </th>		PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	ANG	±1/2"	CAD FILE	M1030991	SIZE	DRAWING NO.
				DIST			B	M1030991.00	REV.	01

D.C. MOTORS




EXTERNAL CONNECTIONS FOR CW ROTATION
 VIEWING LEAD END OF MOTOR WITH RED LEAD
 POSITIVE (+) AND BLACK LEAD NEGATIVE (-)
 FOR CCW ROTATION REVERSE POLARITY

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN IPG 4/8/05 CHK SAD 4/8/05 APPD SCALE 1=1 REF PR040117-RD1 FMF M1120085.00 PREV	
				DEC.	INCHES		TITLE	CONNECTION DIAGRAM
				.X	±.1			
				.XX	±.01			
				.XXX	±.005			
00	RELEASED: REF. PR040117-RD1	IPG 4/8/05	SAD	.XXXX	±.0005	MAT'L.		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2'	FINISH		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	M100530801	
				DIST		SIZE	DRAWING NO.	
						A	M1005308.01	
							REV.	
							00	

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE FOR DIRECT CURRENT PERMANENT MAGNET MOTOR

Model No. <u>CM32D25NZ1</u>	Catalog No. <u>M1125269.00</u>	
HP <u>0.250</u>	RPM <u>42</u>	DC Volts <u>90.0</u>
F.F. <u>1.38</u>	Encl <u>TENV</u>	Type <u>DN</u>
Max. Amb. <u>40.0 Deg C</u>	Insul. <u>F</u>	Frame <u>32</u>
		N.P. FLA <u>2.60</u>
		S.F. <u>1.00</u>
		Duty <u>Cont.</u>



Ra	<u>1.9900</u>	Ohms
La	<u>12.46</u>	mHenrys
Ja	<u>1.883</u>	KG-CM ²
Ke	<u>33.89</u>	V/KRPM

Kt	<u>2.864</u>	LB-IN/AMP
Imax	<u>37.3</u>	AMPS Allowed
FL Torque	<u>280.0</u>	LB-IN
FL EFF	<u>65.30</u>	%

Winding W- MD3227-1B Prepared by V. Boehlen Date 12-06-2010