

PRODUCT INFORMATION PACKET

Model No: M1145033.00

Catalog No: M1145033.00

Parallel Shaft Gearmotor, 0.16 HP, 1 Ph, 60/50 Hz, 115 V, 60 RPM, 38 Frame, TEFC



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E


Nameplate Specifications

Output HP	0.16 Hp	Output KW	0.12 kW
Frequency	60/50 Hz	Voltage	115 V
Current	2.1/1.1 A	Speed	60 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
KVA Code	D	Frame	38
Enclosure	Totally Enclosed Fan Cooled	Thermal Protection	No Protection
Ambient Temperature	40 °C	Drive End Bearing Size	6201
Opp Drive End Bearing Size	6201	UL	Recognized
CSA	Y	CE	Y

Technical Specifications

Rotation	Reversible	Mounting	Special
Shaft Type	Parallel	Overall Length	12.13 in
Frame Length	5.88 in	Shaft Diameter	0.625 in
Shaft Extension	1.5 in	Torque	157 LB-IN
Outline Drawing	M1030381	Connection Drawing	M1005040.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2022



CATALOG NUMBER	OUTPUT RPM	FULL LOAD TORQUE LB.-IN.	INPUT HP	OVERHUNG LOAD LBS.	GEARMOTOR TYPE & FRAME	RATIO TO 1	"XL"	"XH"
M1145030.00	16	391	1/6	399	P243-38	103	12.13	10.63
M1145031.00	30	295	1/6	330	P243-38	58	12.13	10.63
M1145032.00	40	219	1/6	303	P243-38	43	12.13	10.63
M1145033.00	60	157	1/6	268	P242-38	29	12.13	10.63
M1145034.00	90	103	1/6	237	P242-38	19	12.13	10.63
M1145035.00	156	60	1/6	201	P242-38	10.6	12.13	10.63

07	EXTENDED 3 PT MOUNTING HOLES .14" TO MAKE FLUSH	RLW 6/25/02		TOLERANCES UNLESS SPECIFIED	 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN DWF 10/03/94
06	ADDED FANGUARD DIM	BPW 12/19/01		DEC. INCHES		CHK
05	REVD NAMEPLATE APPEARANCE FOR ASSEMBLY	BJB 12/11/01	DWF	.X ±.1		APPD SPV 10/03/94
	CLARITY PER ECR 65231			.XX ±.03		
04	3.50 WAS 3.562, 5.13 WAS 5.19	SPV 04/28/97		.XXX ±.005	TITLE	OUTLINE DRAWING
03	ADDED FLAT TO FAN SHROUD	DWF 09/23/96		.XXXX ±.0005	P240 GEARMOTOR - 38 FRAME A.C.	SCALE 5=8
						REF
NO.	REVISION	BY & DATE	CHK	ANG ±1/2"	MAT'L	FMF M1145030
				FINISH		PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED. THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE	M1030381
				DIST	SIZE B	DRAWING NO. M1030381
						REV 07

