

COMPACT DUAL MEASURING WHEELS

- Dual wheel design for increased balance and more accurate measurements
- Gear-based counter drive is more accurate and durable than the traditional belt drive
- Telescoping handle allows for compact storage
- Glare-resistant counter display is easy to read
- Analog counter dial resets at 10,000 ft.
- Built in kickstand supports wheel for simple measurement recording



Cat. No.	Extended Length	Wheel Diameter	Graduation	Maximum Distance	Product Weight
PSMW28CL	43 in	4 in	Feet and Inches	9999 ft 11 in	1.32

OPEN REEL FIBERGLASS TAPE MEASURES

- Open four-arm frame design protects the blade and does not trap dirt in the case
- Lightweight case for easy handling and transport
- Dual-material grip elevated above the reel prevents contact between reel and knuckles
- Versatile folding end hook for use in multiple applications
- Rewind reel tucks away for protection during storage



Cat. No.	Case Color	Blade Width	Blade Length	Blade Style	Product Weight
FE050D	Rawhide	1/2 in	50 ft	C2	1.38 lb
FE050	Rawhide	1/2 in	50 ft	C1	1.38 lb
FE100	Rawhide	1/2 in	100 ft	C1	1.65 lb
FE100D	Rawhide	1/2 in	100 ft	C2	1.65 lb
FE150	Rawhide	1/2 in	150 ft	C1	1.82 lb
FE150D	Rawhide	1/2 in	150 ft	C2	1.82 lb
FE200	Rawhide	1/2 in	200 ft	C1	2.00 lb
FE200D	Rawhide	1/2 in	200 ft	C2	2.00 lb
FE300	Rawhide	1/2 in	300 ft	C1	2.80 lb
FE300D	Rawhide	1/2 in	300 ft	C2	3.00 lb
FM030CME	Rawhide	13 mm, 1/2 in	30 m, 100 ft	C4	1.47 kg
FM030DM	Rawhide	13 mm, 1/2 in	30 m, 100 ft	C7	1.58 lb
FM030CM	Rawhide	13 mm, 1/2 in	30 m, 100 ft	C3	1.56 lb
FM050CME	Rawhide	13 mm, 1/2 in	50 m, 164 ft	C4	1.75 lb
FM050CM	Rawhide	13 mm, 1/2 in	50 m, 164 ft	C3	1.75 lb
FM060CME	Rawhide	13 mm, 1/2 in	60 m, 200 ft	C4	0.91 kg
FM100CME	Rawhide	13 mm, 1/2 in	100 m, 328 ft	C4	0.72 kg